


This announcement is based on product catalogue information previously shown before its discontinuation.
Product information of the existing product may be different from this version.

Mini 280 terminal layout

- Both SPST and SPDT available
- Plug-in and weatherproof type
- L x W x H = 28 x 28 x 25.5 mm nominal
- 280-terminal type 2.8 x 0.82 mm
- Full automated assembly



■ Type standard

G8W-□□□□-□-□

① ② ③ ④ ⑤ ⑥

	Classification	Symbol	Meaning of the symbol
①	Number of contact poles	1	Number of contact poles
②	Contact structure	A	1a contact
		C	1c contact
③	Protective structure	6	Unsealed (Weather proof type)
		7	Unsealed (In a case)
④	Terminal form	T	Plug-in type
⑤	Bracket	-	Standard case
		F	Metal bracket + Connector guide
⑥	Surge suppressor	R	Built-in resistor

■ Classification

Classification	Terminal form	Contact structure	Protective structure	Rated coil		Type	Bracket
				Voltage (V)	Resistance (Ω)		
Mini 280	Plug-in 280 terminal	SPST (1a)	Unsealed (Weather proof type)	DC12	78	G8W-1A6T-F-R	Metal bracket + Connector guide
			Unsealed (In a case)			G8W-1A7T-R	Standard plug-in
		SPDT (1c)	Unsealed (Weather proof type)			G8W-1C6T-F-R	Metal bracket + Connector guide
			Unsealed (In a case)			G8W-1C7T-R	Standard plug-in

Please confirm Omron Safety Precautions for all automotive relays first.
Omron can not guarantee automotive relays before finish making a contract with product specifications.

■ Ratings

● Operation coil

Rated voltage (V)	Coil resistance (Ω)			Rated current (mA)	Operating voltage (V)	Release voltage (V)	Service voltage range (V)	Rated power consumption (mW)
	Between terminals	Internal coil	Surge suppressor resistance					
DC 12	78	88	1/2W 680	154	8.0 or less	1.0 or more	DC10 to 16	1846

● Switching area

Item		Performance
Contact material		Silver alloy
Rated voltage		DC12V
Rated load	N.O. side	Resistance load, 35A
	N.C. side	Resistance load, 20A
Inrush current	N.O. side	120A
	N.C. side	40A
Continuous carry current ^{*1}	N.O. side	35A
	N.C. side	20A
Min. Carry / Switching Current	DC12V 1A	

■ Performance

Item		Standard value
Voltage drop between terminals	N.O. side	50mV or less, 10A
	N.C. side	50mV or less, 10A
Operating time ^{*2}		Max. 10ms at 14V (Normally 5.6 ms)
Release time ^{*2}		Max. 10ms at 14V (Normally 1.4 ms)
Insulation resistance ^{*3}	Between coil and terminal	20MΩ or more
	Between homopolar contacts	20MΩ or more
Withstand voltage ^{*4}	Between coil and terminal	AC500V, for 1 minute
	Between homopolar contacts	AC500V, for 1 minute
Vibration tolerance	Durability	33Hz 43.1m/s ²
	Malfunction	20 to 500Hz 43.1m/s ²
Mechanical endurance		1,000,000 times
Electrical endurance		100,000 times
Ambient temperature		-40 to +125°C
Ambient humidity		35 to 95%RH
Weight		Approx. 34.0g

■ Packing

Packing form	Tray
MOQ ^{*5}	336pcs (48pcs to 7 trays)

Note: All values above are measured in early time under an ambient temperature of +20°C and humidity of 65% unless stated.

*1. The value stated is at maximum temperature in a guaranteed ambient temperature.

*2. Bounce time is not included.

*3. Measured at DC500V.

*4. Measured under 1mA of leak current, 50/60Hz for 1 minute.

*5. Minimum Order Quantity is subject to change, please feel free to contact our sales representatives.

Please confirm Omron Safety Precautions for all automotive relays first.
Omron can not guarantee automotive relays before finish making a contract with product specifications.




This announcement is based on product catalogue information previously shown before its discontinuation.
Product information of the existing product may be different from this version.

Dimensions (Unit: mm)

G8W-1A7T-R






Terminal arrangement /
Internal connections
(BOTTOM VIEW)



G8W-1C7T-R



Terminal arrangement /
Internal connections
(BOTTOM VIEW)




Tolerance unless otherwise specified
Less than 1 mm: ±0.1 mm
Less than 1 to 3 mm: ±0.2 mm
3 mm or more: ±0.3 mm

Please confirm Omron Safety Precautions for all automotive relays first.
Omron can not guarantee automotive relays before finish making a contract with product specifications.

This announcement is based on product catalogue information previously shown before its discontinuation.
Product information of the existing product may be different from this version.

G8W-1A6T-F-R
G8W-1C6T-F-R



Tolerance unless otherwise specified
Less than 1 mm: ± 0.1 mm
Less than 1 to 3 mm: ± 0.2 mm
3 mm or more: ± 0.3 mm

Please confirm Omron Safety Precautions for all automotive relays first.
Omron can not guarantee automotive relays before finish making a contract with product specifications.