

Technical data sheet

Article number:
170-20400

HEGPA6604



Product Group	Polamide 6.6 Braided Sleeving
Product Family	Helagain HEGPA66
Material	Polyamide 6.6 (PA66)
Colour	Grey (GY)
Application Method	Fraying of the braided sleeving can be avoided by using a hot-knife to cut the sleeving. Braided sleeving can also be supplied in pre-cut lengths on request.
Bundle Ø max.	6 mm
Bundle Ø min.	3 mm
Melting Point	+255 °C
Operating Temperature	-60 °C to +150 °C
Package Content	200 m
Package Content packed in	pack

HF ✓

RoHS ✓