


REV.	DESCRIPTION/ECO NO.	DATE
	RELEASE	1/27/14
A	ADD SIDE VIEW	8/20/15



NOTES:

1. OPERATION


- GENTLY LIFT LATCH AT SIDE OF CONNECTOR.
- SWING COVER OFF OF CONTACTS.
- SLIDE THE FLEX TAPE INTO THE CONNECTOR PLACING THE EDGE OF THE FLEX TAPE UNDER 2 HOLD DOWN TABS. MAKE SURE THE POLARITY IS MATCHED BETWEEN THE FLEX TAPE AND THE CONNECTOR COVER.
- FOLD OVER THE COVER AND PRESS IN PLACE UNTIL THE LATCH IS FULLY ENGAGED.

- LIMIT CURRENT TO A MAXIMUM OF 5 AMPS.

4 PIN JOINER CONNECTOR
WIRE TYPE: UL1007, 22 AWG

USED WITH JKL RGB LED FLEX LIGHT RIBBON
PART NO.: ZFS-10504-RGB

JKL PART NO.: ZCH-170-RGB-J

METRIC  THIRD ANGLE PROJECTION		DIMENSIONS ARE IN mm (INCHES) TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- REF. 2 PL +/- REF. ANGLE +/- 0		JKL COMPONENTS CORPORATION								
		TITLE		RGB FLEX RIBBON JOINER CONNECTOR HARNESS								
DRAWN BY L. WENGSTROM		APPV'D BY L.R.		DATE 8/20/15		SIZE A	FSCM NO. 55335	DRAWING NO. ZCH-170-RGB-J				
- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED				SCALE NONE	RELEASED DATE 1/27/14	REVISION DATE 8/20/15		REV. NO. A	SHEET 1 OF 1			