



1							2							3							4						
	PART NO.	DIM.A	DIM.B	DIM.C	DIM.D	DIM.E		PART NO.	DIM.A	DIM.B	DIM.C	DIM.D	DIM.E		PART NO.	DIM.A	DIM.B	DIM.C	DIM.D	DIM.E		PART NO.	DIM.A	DIM.B	DIM.C	DIM.D	DIM.E
20Pos	10153118-Y20XALF	22.00	24.00	22.00	13.80	20.78	26Pos	10153118-Y26XALF	27.40	29.40	27.40	13.80	27.98	34Pos	10153118-Y34XALF	34.60	36.60	34.60	13.80	33.38	36Pos	10153118-Y36XALF	36.40	38.40	36.40	13.80	35.18
	10153118-Y20XBLF				16.60	20.78		10153118-Y26XBLF				23.80	27.98		10153118-Y34XBLF				29.20	33.38		10153118-Y36XBLF				31.00	35.18
	10153118-Y20XCFL				13.80	19.30		10153118-Y26XCFL				13.80	26.50		10153118-Y34XCFL				13.80	31.90		10153118-Y36XCFL				13.80	33.70
	10153118-Y20XDLF				15.20	19.30		10153118-Y26XDLF				22.40	26.50		10153118-Y34XDLF				27.80	31.90		10153118-Y36XDLF				29.60	33.70
22Pos	10153118-Y22XALF	23.80	25.80	23.80	13.80	22.58	28Pos	10153118-Y28XALF	29.20	31.20	29.20	13.80	26.18	38Pos	10153118-Y38XALF	38.20	40.20	38.20	13.80	36.98	40Pos	10153118-Y40XALF	40.00	42.00	40.00	13.80	38.78
	10153118-Y22XBLF				18.40	22.58		10153118-Y28XBLF				22.00	26.18		10153118-Y38XBLF				32.80	36.98		10153118-Y40XBLF				34.60	38.78
	10153118-Y22XCFL				13.80	21.10		10153118-Y28XCFL				13.80	24.70		10153118-Y38XCFL				13.80	35.50		10153118-Y40XCFL				13.80	37.30
	10153118-Y22XDLF				17.00	21.10		10153118-Y28XDLF				20.60	24.70		10153118-Y38XDLF				31.40	35.50		10153118-Y40XDLF				33.20	37.30
24Pos	10153118-Y24XALF	25.60	27.60	25.60	13.80	24.38	30Pos	10153118-Y30XALF	31.00	33.00	31.00	13.80	29.78	32Pos	10153118-Y32XALF	32.80	34.80	32.80	13.80	31.58	36Pos	10153118-Y36XALF	36.40	38.40	36.40	13.80	35.18
	10153118-Y24XBLF				20.20	24.38		10153118-Y30XBLF				25.60	29.78		10153118-Y32XBLF				27.40	31.58		10153118-Y36XBLF				31.00	35.18
	10153118-Y24XCFL				13.80	22.90		10153118-Y30XCFL				13.80	28.30		10153118-Y32XCFL				13.80	30.10		10153118-Y36XCFL				13.80	33.70
	10153118-Y24XDLF				18.80	22.90		10153118-Y30XDLF				24.20	28.30		10153118-Y32XDLF				26.00	30.10		10153118-Y36XDLF				29.60	33.70
REMARK, THIS SHEET SHOWS 20Pos. TO 40Pos.																											

A CODE / COLOR:BLACK	B CODE / COLOR:GREEN;COLOR CODE: RAL6002	C CODE / COLOR:WHITE;COLOR CODE: RAL9001	D CODE /COLOR: BORDEAUX;COLOR CODE:RAL4004
REMARK, THIS SHEET SHOWS 20Pos. TO 40Pos.			




mat'l. code				surface ISO 1302 ✓	tolerance ISO 406/ISO 1101	projection 	product family HPL649			
ltr	ecn no	dr	date	tolerances unless otherwise specified		mm 	title PIN HEADER,DUAL ROW,THT WireLock® Series R/A Connector			
J				angles	.0±.5		dwg no 10153118 sheet2 of 3 size A4			
				linear	.00±.25					
				0°±2°	.000±.010					
				dr	NICK ZHANG	05/22/19	Amphenol FCI			
				engr	NICK ZHANG	05/22/19				
				chr	ZK HU	05/22/19				
				appd	TIM YAO	05/22/19	type Product Customer Drawing			
sheet index	revision	J								
	sheet	1~3								

	A CODE / COLOR:BLACK	B CODE / COLOR:GREEN;COLOR CODE: RAL6002	C CODE / COLOR:WHITE;COLOR CODE: RAL9001	D CODE /COLOR: BORDEAUX;COLOR CODE:RAL4004
14POS 16POS				
18POS				

	PART NO.	DIM.A	DIM.B	DIM.C	DIM.E		PART NO.	DIM.A	DIM.B	DIM.C	DIM.E		PART NO.	DIM.A	DIM.B	DIM.C	DIM.D	DIM.E
14Pos.	10153118-Y14XALF	16.60	18.60	16.60	15.38	16Pos.	10153118-Y16XALF	18.40	20.40	18.40	17.18	18Pos.	10153118-Y18XALF	20.20	22.20	20.20	6.14	18.98
	10153118-Y14XBLF				13.78		10153118-Y16XBLF				15.58		10153118-Y18XBLF					14.30
	10153118-Y14XCLF				13.90		10153118-Y16XCLF				15.70		10153118-Y18XCLF				6.14	18.98
	10153118-Y14XDLF				12.33		101532118-Y16XDLF				14.13		10153118-Y18XDLF					16.63

	A CODE / COLOR:BLACK
10Pos.	
12Pos.	

	PART NO.	DIM.A	DIM.B	DIM.C	DIM.E
10Pos.	10153118-Y10XALF	13.00	15.00	12.80	11.78
12Pos.	10153118-Y12XALF	14.80	16.80	14.80	13.03
REMARK, FOR 10 Pos. TO 12 Pos., ONLY PROVIDE A CODE.					



mat'l. code				surface ISO 1302 ✓	tolerance ISO 406/ISO 1101	projection 	product family HPL649			
ltr	ecn no	dr	date	tolerances unless otherwise specified		 mm scale 1:1	title PIN HEADER,DUAL ROW,THT WireLock® Series R/A Connector			
J				angles	.0±.5		dwg no 10153118 sheet3 of 3 size A4			
				linear	.00±.25					
				0°±2°	.000±.010					
				dr	NICK ZHANG	05/22/19				
				engr	NICK ZHANG	05/22/19				
				chr	ZK HU	05/22/19				
				appd	TIM YAO	05/22/19				
sheet index	revision	J					type Product Customer Drawing			
	sheet	1~3								