


 **Live Product Chat** US Only  
8:30am - 5pm ET, Mon - Fri



TE Part Number: 1-827880-2

Active

Add to Part List

 Always EU RoHS/ELV Compliant (Statement of Compliance)

- Header
- Number of Positions = 26
- Right Angle Mount Angle
- Right Side Cable Entry Angle
- Header Type = Pin

[View all Features](#) | [Find Similar Products](#)

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

- [MODU II Stiftwanne, 26-polig \(PDF, English\)](#)

- None Available

- None Available

- None Available

- None Available

- 2D Drawing (DXF, Version H3)
- 3D Model (IGES, Version H3)
- 3D Model (STEP, Version H3)

## List all Documents

- Product Line Information

- Tooling

- Product Type = Header
- Number of Positions = 26
- Mount Angle = Right Angle
- Color = White
- Material = Polyamide 6.6
- Mounting Ears = With
- Pin/Socket = Pin
- PCB Mount Style = Thru Hole

- Termination End Plating = Tin
- Termination (Solder) Post Length (mm [in]) = 3.50 [0.138]

- Cable Entry Angle = Right Side
- Header Type = Pin
- Centerline, Matrix (mm [in]) = 2.54 x 2.54  
[.100 x .100]
- Number of Rows = 2

- Contact Finish = Tin

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

- Terminate To = Printed Circuit Board

- Brand = AMP