



Part Number : [740990011](#)

Product Description : SL Wire-to-Board Header, Surface Mount, Single Row, Vertical, 3.05mm Pocket, Shrouded, 11 Circuits, Tin (Sn) Plating

Series Number : 74099

Status : Active

Product Category : PCB Headers and Receptacles



Documents and Resources

Drawings

[740990011_sd.pdf](#)

[PK-70873-003-001.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

Specifications


[PS-70400-001.pdf](#)

[PS-70541-001.pdf](#)

[TS-70541-100-001.pdf](#)

Product Environment Compliance

Compliance

| | |
|--------------------|---|
| GADSL/IMDS | Not Relevant |
| China RoHS |  per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

| | |
|----------------|--|
| Status | Active |
| Category | PCB Headers and Receptacles |
| Series | 74099 |
| Description | SL Wire-to-Board Header, Surface Mount, Single Row, Vertical, 3.05mm Pocket, Shrouded, 11 Circuits, Tin (Sn) Plating |
| Application | Wire-to-Board |
| Component Type | PCB Header |
| Product Name | SL |
| UPC | 756054640357 |

Agency

| | |
|-----|---------|
| CSA | LR19980 |
| UL | E29179 |

Electrical

| | |
|-------------------------------|------|
| Current - Maximum per Contact | 3.0A |
| Voltage - Maximum | 250V |

Physical

| | |
|--------------------------------|--------------------------------|
| Breakaway | No |
| Circuits (Loaded) | 11 |
| Circuits (maximum) | 11 |
| Color - Resin | Black |
| Durability (mating cycles max) | 25 |
| First Mate / Last Break | No |
| Glow-Wire Capable | No |
| Material - Metal | Brass, Phosphor Bronze |
| Material - Plating Mating | Tin |
| Material - Plating Termination | Tin |
| Material - Resin | High Temperature Thermoplastic |
| Net Weight | 2.153/g |
| Number of Rows | 1 |
| Orientation | Vertical |
| Packaging Type | Tube |
| PCB Thickness - Recommended | 1.60mm |
| Pitch - Mating Interface | 2.54mm |
| Plating min - Mating | 3.810µm |
| Plating min - Termination | 3.810µm |
| Polarized to Mating Part | Yes |
| Shrouded | Shrouded |
| Temperature Range - Operating | -40° to +105°C |
| Termination Interface Style | Surface Mount |

Solder Process Data

| | |
|------------------------------|--------|
| Max-Duration | 40 |
| Lead-Free Process Capability | REFLOW |
| Max-Cycle | 3 |
| Max-Temp | 245 |

Mates With / Use With

Mates with Part(s)

| Description | Part Number |
|-------------|-------------|
|-------------|-------------|

| | |
|---|--------------|
| SL Single Row Crimp Housings and CPA Retainers | <u>70066</u> |
| SL Single Row Female Insulation Displacement Connector Assemblies | <u>70400</u> |
| SL Single Row Female Receptacles | <u>70430</u> |

This document was generated on May 27, 2026