



RDIMM

M393A8G40AB2-CVF



OVERVIEW

SPECIFICATIONS

RELATED RESOURCES

RELATED INSIGHTS

Proven DRAM Module Solution in the Global Market

Samsung’s memory modules are designed for a wide range of applications to deliver the best performance with low power requirements.

- RDIMM
 - UDIMM
 - ECC UDIMM / ECC SODIMM
- LRDIMM
 - SODIMM

Specifications

DDR	DDR4	Dimm Type	RDIMM
Density	64GB	Rank x Org.	2R x 4
Speed	2933 Mbps	Voltage	1.2 V
No. of Pin	288	Component Composition	(4G x 4) x 36
Product Status	Sample		

SEE ALL

Related Insights



Samsung Electronics Hosts “Samsung Future Tech Forum” in

Samsung held the “Samsung Future Tech Forum” in Beijing, China, showcasing its “AI”-optimized component solutions.

[LEARN MORE >](#)



Samsung’s latest 3DS/TSV DRAM technology boosting the

The impact of Samsung’s latest 3DS/TSV DRAM technology, built into Lenovo’s cutting-edge servers, for typical environments running SAP S/4HANA and SAP Bank Analyzer

[LEARN MORE >](#)



All product specifications reflect internal test results and are subject to variations by user’s system configuration. All product images shown are for illustration purposes only and may not be an exact representation of the product. Samsung reserves the right to change product images and specifications at any time without notice.

Insights

[Product Finder](#)

[Technical Resources](#)

[TCO Calculator](#)

[About Us](#)

PRODUCTS

[DRAM](#)

[SSD](#)

[eSTORAGE](#)

[MCP](#)

[PROCESSOR](#)

[IMAGE SENSOR](#)

[SECURITY SOLUTIONS](#)

[DISPLAY IC](#)

[POWER IC](#)

SOLUTIONS

[APPLICATIONS](#)

Global Sites

[Samsung Business](#)


[Exynos](#)

[LED](#)

[Display](#)

[Worker Safety](#)

Follow us



This website is best viewed using Microsoft Internet Explorer 9 or higher, and/or latest version of Google Chrome and Mozilla Firefox browsers.