

Modular Rack Cabinet System (1500 lb) C2 Series

Modular rack cabinet system designed for flexible configuration, allowing users to select frames, panels, rails, and accessories to build a complete solution.



Key Features and Benefits

- 14-gauge steel cabinet frame with 12-gauge reinforced corner brackets and 16-gauge doors and panels (1500 lb **capacity**) provides durable support for equipment installations.
- Modular cabinet system design allows users to select frames, mounting rails, panels, doors, and accessories to build a fully customized solution.
- Available with square hole or 10-32 threaded **combination** mounting rails (12-gauge or 10-gauge steel) supports a wide range of equipment and installation requirements.
- Infinite-depth rail adjustment using C-channel struts supports flexible equipment mounting and configuration.
- Wide range of sizes (20U–49U, multiple depths and widths) supports applications from compact installations to full-height cabinet systems.
- Interchangeable top and bottom panels (solid, vented, fan, or cable entry) support airflow management and cable routing customization.
- Optional doors (solid, vented, window) and side panels allow customization of airflow, visibility, and security.
- Extensive accessory ecosystem (cable management, shelves, PDUs, drawers) supports full system integration and scalability.
- Four (4) leveling feet included with support for optional casters supports stable installation and mobility options.
- Grounding studs on frame, doors, and panels support bonding and safe installation.
- TAA-compliant, manufactured in North America supports government procurement requirements and ensures consistent quality.
- Textured powder coat finish (GREENGUARD, TSCA, RoHS compliant) supports indoor air quality and environmental compliance.

The C2 Series modular rack cabinet system provides a flexible solution for building custom cabinet configurations for AV, telecom, lab, and equipment installations. With a 1500 lb load capacity and a wide range of configurable components, it allows users to design cabinets tailored to their specific requirements.

Featuring interchangeable panels, multiple rail options, and extensive accessory compatibility, the C2 system supports scalable deployments where flexibility and customization are critical.

When another product may be a better choice

- When you need a fully assembled version of this platform, consider our **C2RR** Series.
- When you need a cabinet designed for server and sliding rail compatibility, consider our **C4** or **H1** Series.
- When you need a pre-configured cabinet for data center deployments, consider our **C4RR-A** or **C4RR-D** Series.

Upgrade your cabinet to include Lifting Eye-Bolts with 2,000 lbs of lifting



capacity. Ask your local representative for details.

Accessories

- Cabinet Baying & Joining Kit for C2 Cabinets
- Door Adapter Kit
- Partial Height Door Support
- Vertical Cable Tray with Optional PDU Mount for Server Cabinets
- Locking Rack Storage Drawer
- Horizontal Hinged Cable Manager with Door
- Horizontal Cable Lacing Bar Steel Cable Support Bar
- Bonding and Grounding
- Hardware for Rack Mounting Solutions
- C2 Low-Profile Cabinet Caster Set
- Cable Management Arm Hinged for Sliding Rack Equipment
- Rack Cabinet Top Panels Solid, Cable Entry and Fan Panels
- Side Panel Locking Kit
- Cabinet Door Replacement Lock
- Rack Shelves
- Horizontal Cable Manager Ring Style
- Rack Panels for Rack Optimization
- Horizontal Cable Management Bar Steel Cable Support Bar
- Power Distribution Units (PDUs)
- Rack and Cabinet Caster Set
- Chassis Handles
- Rack & Cabinet Bolt Down Kits

C2 Open Frames (Mounting Rails Not Included)

Part No.	Part No.	Overall Dimensions			Rack	Usable Mounting Dimensions		19" Rack Rails (Pairs)	
RAL 9005 Black	RAL 7035 Light Gray	Height	Width	Depth	Units	Height	Depth	Tapped 10-32	Square Hole
C2F193523BK1	C2F193523LG1	43.16	23.00	23.62	20U	35.06	21.63	CCR35TZPL	CPR35SZPL
C2F193531BK1	C2F193531LG1	43.16	23.00	31.50	20U	35.06	29.50	CCR35TZPL	CPR35SZPL
C2F193536BK1	C2F193536LG1	43.16	23.00	36.00	20U	35.06	34.00	CCR35TZPL	CPR35SZPL
C2F194223BK1	C2F194223LG1	50.16	23.00	23.62	24U	42.06	21.63	CCR42TZPL	CPR42SZPL
C2F194231BK1	C2F194231LG1	50.16	23.00	31.50	24U	42.06	29.50	CCR42TZPL	CPR42SZPL
C2F194236BK1	C2F194236LG1	50.16	23.00	36.00	24U	42.06	34.00	CCR42TZPL	CPR42SZPL
C2F194923BK1	C2F194923LG1	57.16	23.00	23.62	28U	49.06	21.63	CCR49TZPL	CPR49SZPL
C2F194931BK1	C2F194931LG1	57.16	23.00	31.50	28U	49.06	29.50	CCR49TZPL	CPR49SZPL
C2F194936BK1	C2F194936LG1	57.16	23.00	36.00	28U	49.06	34.00	CCR49TZPL	CPR49SZPL
C2F195623BK1	C2F195623LG1	64.16	23.00	23.62	32U	56.06	21.63	CCR56TZPL	CPR56SZPL
C2F195631BK1	C2F195631LG1	64.16	23.00	31.50	32U	56.06	29.50	CCR56TZPL	CPR56SZPL
C2F195636BK1	C2F195636LG1	64.16	23.00	36.00	32U	56.06	34.00	CCR56TZPL	CPR56SZPL
C2F196323BK1	C2F196323LG1	71.16	23.00	23.62	36U	63.06	21.63	CCR63TZPL	CPR63SZPL
C2F196331BK1	C2F196331LG1	71.16	23.00	31.50	36U	63.06	29.50	CCR63TZPL	CPR63SZPL
C2F196336BK1	C2F196336LG1	71.16	23.00	36.00	36U	63.06	34.00	CCR63TZPL	CPR63SZPL
C2F197023BK1	C2F197023LG1	78.16	23.00	23.62	40U	70.06	21.63	CCR70TZPL	CPR70SZPL
C2F197031BK1	C2F197031LG1	78.16	23.00	31.50	40U	70.06	29.50	CCR70TZPL	CPR70SZPL
C2F197036BK1	C2F197036LG1	78.16	23.00	36.00	40U	70.06	34.00	CCR70TZPL	CPR70SZPL
C2F197823BK1	C2F197823LG1	86.91	23.00	23.62	45U	78.81	21.63	CCR78TZPL	CPR78SZPL
C2F197831BK1	C2F197831LG1	86.91	23.00	31.50	45U	78.81	29.50	CCR78TZPL	CPR78SZPL
C2F197836BK1	C2F197836LG1	86.91	23.00	36.00	45U	78.81	34.00	CCR78TZPL	CPR78SZPL
C2F198523BK1	C2F198523LG1	93.91	23.00	23.62	49U	85.81	21.63	CCR85TZPL	CPR85SZPL
C2F198531BK1	C2F198531LG1	93.91	23.00	31.50	49U	85.81	29.50	CCR85TZPL	CPR85SZPL
C2F198536BK1	C2F198536LG1	93.91	23.00	36.00	49U	85.81	34.00	CCR85TZPL	CPR85SZPL

C2 Doors

Door Type	Part No.	Part No.	Use with Cabinet	
	Black	RAL 7035 Light Gray	Rack Units	Height
Solid	CDF1935SBK1	CDF1935SLG1	20U	35.00
	CDF1942SBK1	CDF1942SLG1	24U	42.00
	CDF1949SBK1	CDF1949SLG1	28U	49.00
	CDF1956SBK1	CDF1956SLG1	32U	56.00
	CDF1963SBK1	CDF1963SLG1	36U	63.00

Door Type	Part No.	Part No.	Use with Cabinet	
	Black	RAL 7035 Light Gray	Rack Units	Height
	CDF1970SBK1	CDF1970SLG1	40U	70.00
	CDF1978SBK1	CDF1978SLG1	45U	78.75
Louver Vented Door	CDF1935LBK1	CDF1935LLG1	20U	35.00
	CDF1942LBK1	CDF1942LLG1	24U	42.00
	CDF1949LBK1	CDF1949LLG1	28U	49.00
	CDF1956LBK1	CDF1956LLG1	32U	56.00
	CDF1963LBK1	CDF1963LLG1	36U	63.00
	CDF1970LBK1	CDF1970LLG1	40U	70.00
	CDF1978LBK1	CDF1978LLG1	45U	78.75
Vented Door	CDF1985LBK1	CDF1985LLG1	49U	85.75
	CDF1970VBK1	CDF1970VLG1	40U	70.00
	CDF1978VBK1	CDF1978VLG1	45U	78.75
Window Door	C2DF1935PBK1	Not Available	20U	35.00
	C2DF1942PBK1	Not Available	24U	42.00
	C2DF1949PBK1	Not Available	28U	49.00
	C2DF1956PBK1	Not Available	32U	56.00
	C2DF1963PBK1	Not Available	36U	63.00
	C2DF1970PBK1	C2DF1970PLG1	40U	70.00
	C2DF1978PBK1	Not Available	45U	78.75
	C2DF1985PBK1	Not Available	49U	85.75
Vented Window Door	CDF1970VPBK1	CDF1970VPLG1	40U	70.00
	CDF1978VPBK1	CDF1978VPLG1	45U	78.75

C2 Side Panels (Sold in Pairs)

Part No.	Part No.	Use with Cabinet Frame			
	Black	RAL 7035 Light Gray	Rack Units	Height	Depth
CSP3523BK1	CSP3523LG1		20U	35.00	23.63
CSP4223BK1	CSP4223LG1		24U	42.00	23.63
CSP4923BK1	CSP4923LG1		28U	49.00	23.63
CSP5623BK1	CSP5623LG1		32U	56.00	23.63
CSP6323BK1	CSP6323LG1		36U	63.00	23.63
CSP7023BK1	CSP7023LG1		40U	70.00	23.63
CSP7823BK1	CSP7823LG1		45U	78.75	23.63
CSP8523BK1	CSP8523LG1		49U	85.75	23.63
CSP3531BK1	CSP3531LG1		20U	35.00	31.50
CSP4231BK1	CSP4231LG1		24U	42.00	31.50
CSP4931BK1	CSP4931LG1		28U	49.00	31.50
CSP5631BK1	CSP5631LG1		32U	56.00	31.50
CSP6331BK1	CSP6331LG1		36U	63.00	31.50
CSP7031BK1	CSP7031LG1		40U	70.00	31.50
CSP7831BK1	CSP7831LG1		45U	78.75	31.50
CSP8531BK1	CSP8531LG1		49U	85.75	31.50
CSP3536BK1	CSP3536LG1		20U	35.00	36.00
CSP4236BK1	CSP4236LG1		24U	42.00	36.00
CSP4936BK1	CSP4936LG1		28U	49.00	36.00
CSP5636BK1	CSP5636LG1		32U	56.00	36.00
CSP6336BK1	CSP6336LG1		36U	63.00	36.00
CSP7036BK1	CSP7036LG1		40U	70.00	36.00
CSP7836BK1	CSP7836LG1		45U	78.75	36.00
CSP8536BK1	CSP8536LG1		49U	85.75	36.00

To lock side panels, order Part No. CSPQTRL

C2 Top Panels

Part No.	Part No.	Use with Cabinet		
	Black	RAL 7035 Light Gray	Top Panel Type	Depth
C2T1923SBK1	C2T1923SLG1		Solid Top	23.00
C2T1931SBK1	C2T1931SLG1			23.62
C2T1936SBK1	C2T1936SLG1			31.50
C2T1923VBK1	C2T1923VLG1		Vented Top	23.00
C2T1931VBK1	C2T1931VLG1			23.62
C2T1936VBK1	C2T1936VLG1			31.50
C2T1923VCEBK1	C2T1923VCELG1		Vented Top With 3x 3.5" Cable Entry Holes	23.00
C2T1931VCEBK1	C2T1931VCELG1			23.62

Part No.	Part No.	Use with Cabinet		
Black	RAL 7035 Light Gray	Top Panel Type	Width	Depth
C2T1936VCEBK1	C2T1936VCELG1		23.00	36.00
C2T1923RBK1	C2T1923RLG1	Raised Top Allows passive cooling and protects from falling debris	23.00	23.62
C2T1931RBK1	C2T1931RLG1		23.00	31.50
C2T1936RBK1	C2T1936RLG1		23.00	36.00

C2 Bottom Panels

Part No.	Part No.	Use with Cabinet Frame		
RAL9005 Black	RAL7035 Light Gray			
C2BPS1923BK1	C2BPS1923LG1		C2F19xx23xx	
C2BPS1931BK1	C2BPS1931LG1		C2F19xx31xx	
C2BPS1931BK1	C2BPS1931LG1		C2F19xx36xx	

Note: The bottom panels for 31" and 36" deep frames are the same and this is why there is no 36" depth bottom panel.

Replacement Lock Kit for C2 Door

Part No.	CDQTRL
----------	--------

Lock Kit for C2 Side Panel

Part No.	CSPQTRL
----------	---------

Where the series works best

- AV and media installations.
- Telecom and legacy network environments.
- Test and measurement applications.
- Industrial and automation systems.
- Projects requiring custom cabinet configurations.

Tags: **modular rack cabinet, rack cabinet system, equipment cabinet, AV rack cabinet, telecom cabinet, network cabinet, rack enclosure, 19 inch cabinet, configurable cabinet system**

© 2026. Hammond Manufacturing Ltd. All rights reserved.

Ganging/Joining Kit

Part No.	CGH01
----------	-------

Plinth

RAL 9005 Black	RAL 7035 Light Gray	Overall	Use with Cabinet
Part No.	Part No.	Height	Depth
CPL19423BK1	CPL19423LG1	4.00	23.63
CPL19431BK1	CPL19431LG1	4.00	31.50
CPL19436BK1	CPL19436LG1	4.00	36.00

Applications and when to use the series

- Applications needing custom combinations of rails, panels, and accessories.
- Environments where equipment requirements vary or evolve over time.
- Deployments requiring flexible airflow, cable management, and access options.
- Installations supporting AV, telecom, lab, or general equipment.

Data subject to change without notice.