






REV.	DATE	DESCRIPTION
NC	08/25/00	INITIAL RELEASE
A	10/04/07	REVISE FERRULE DIMENSIONS, UPDATE DRAWING FORMAT



NOTE:

1. CRIMPED FERRULE HEX CRIMP SIZE .128"
2. CONTACT PIN TO SOLDER.

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex					
8						DRAWN	G.R.S.	10/04/07							
7						CHECKED			PART DESCRIPTION						
6	HEAT SHRINK TUBE			1		ISSUED									
5	FERRULE	COPPER	NICKEL	1		SHEET			1 OF 1		SMC R/A CRIMP PLUG (RG-174/U, 188A/U, 316/U)				
4	COVER	BRASS	NICKEL	1											
3	CONTACT PIN	BER. COPPER	GOLD	1							PART NO. 152106				
2	INSULATOR	TEFLON	NATURAL	1											
1	BODY	BRASS	NICKEL	1						DWG. NO. 152106.DWG REV. A SIZE A SCALE NA					
	DESCRIPTION	MATERIAL	FINISH	QTY				CAD FILE C:/152/152106.DWG							