



+ RELAYS, CONTACTORS & SWITCHES

TO-5/.100 GRID



✓ Active

TE CONNECTIVITY (TE)

JMGAC-26PW = M39016/17-042P

1-1617145-2

TE Internal Number: 1-1617145-2

Mil-Spec: M39016/17-042P

Alias ID: JMGAC-26PW

Not EU RoHS Compliant

Not EU ELV Compliant

Contact Arrangement 2 Form C, DPDT, 2 C/O

Input Voltage (VDC) 14.2

Coil Suppression Diode Without

MOSFET Driver Without

Transistor Driver With

DOCUMENTATION —

No documentation available.

FEATURES +

Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features

MOSFET Driver Without

Product Type Relay

Relay Type Military/Aerospace High Performance

Coil Latching Without

Enclosure Type Hermetically Sealed

Configuration Features

Transistor Driver With

Electrical Characteristics

Input Voltage (VDC) 14.2
Coil Suppression Diode Without
Coil Voltage (VDC) 26.5
Coil Resistance (Ω) 1560
Coil Power Rating (DC) (mW) 450
Coil Polarity Protection Diode Without
Contact Switching Voltage (Max) 28
Actuating System DC
Coil Power Measurement Milliwatts
Shock 75G's, 6ms
Vibration 30G's, 10 – 3000Hz
Coil Magnetic System Non-Polarized, Monostable

Contact Features

Contact Arrangement 2 Form C, DPDT, 2 C/O
Contact Current Rating (A) 1
Contact Current Class Low Level – 1 A
Pin Configuration .175" Diameter Mounting Pad

Termination Features

Termination Type PC Pins

Mechanical Attachment

Mounting Type Printed Circuit Board

Usage Conditions

Operating Temperature Range ($^{\circ}\text{C}$) -65 – 125

Statement of Compliance

Statement of Compliance

PDF