

 [Live Product Chat](#)



✓ Active

 Add to Part List

Not EU RoHS or ELV Compliant (Find RoHS Compliant Alternates)

- Socket
- Mating Pin Dia. Range = .36 - .66 mm
- Socket Length = 4.52 mm
- Sleeve Style = Closed Bottom
- Tin Sleeve Plating

[View all Features](#) | [Find Similar Products](#)

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

- [MINIATURE SPRING SOCKET ASSEMBLY, SERIES 2](#) (PDF, English)

- None Available

- None Available

- [Miniature Spring Socket Contacts \(PDF, English\)](#)

- None Available

- None Available

- Product Line Information

- Tooling

List all Documents

- Product Type = Socket
- Socket Length (mm [in]) = 4.52 [0.178]
- Sleeve Style = Closed Bottom
- Sealant = Without
- Sleeve Material = Copper
- Recommended Hole Size (mm [in]) = 1.32 [0.052]

- Mating Pin Dia. Range (mm [in]) = 0.36 – 0.66
[0.014 – 0.026]
- Spring Material = Beryllium Copper

- Sleeve Plating = Tin
- Contact Spring Plating = Gold (30)
- Contact Material = Beryllium Copper

- Insertion Method = Hand/Semi-Automatic

- Government/Industry Qualification = No
- RoHS/ELV Compliance = Not ELV/RoHS compliant
- Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C, Reflow solder capable to 245°C, Reflow solder capable to 260°C, Pin-in-Paste capable to 245°C, Pin-in-Paste capable to 260°C

- Application = Production

- Packaging Method = Loose Piece

- Brand = AMP