

# MOSFET – Dual, N-Channel, Small Signal

20 V, 540 mA

NTZD3154N

## Features

- Low  $R_{DS(on)}$  Improving System Efficiency
- Low Threshold Voltage
- Small Footprint 1.6 x 1.6 mm
- ESD Protected Gate
- These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant

## Applications

- Load/Power Switches
- Power Supply Converter Circuits
- Battery Management
- Cell Phones, Digital Cameras, PDAs, Pagers, etc.

**MAXIMUM RATINGS** ( $T_J = 25^\circ\text{C}$  unless otherwise noted.)

| Parameter                                                         | Symbol         | Value                         | Unit             |
|-------------------------------------------------------------------|----------------|-------------------------------|------------------|
| Drain-to-Source Voltage                                           | $V_{DS}$       | 20                            | V                |
| Gate-to-Source Voltage                                            | $V_{GS}$       | $\pm 7.0$                     | V                |
| Continuous Drain Current (Note 1)                                 | $I_D$          | $T_A = 25^\circ\text{C}$      | 540              |
|                                                                   |                | $T_A = 85^\circ\text{C}$      | 390              |
| Power Dissipation (Note 1)                                        | $P_D$          | 250                           | mW               |
| Continuous Drain Current (Note 1)                                 | $I_D$          | $t \leq 5\text{ s}$           | 570              |
|                                                                   |                | $T_A = 85^\circ\text{C}$      | 410              |
| Power Dissipation (Note 1)                                        | $P_D$          | $t \leq 5\text{ s}$           | 280              |
| Pulsed Drain Current                                              | $I_{DM}$       | $t_p = 10\text{ }\mu\text{s}$ | 1.5              |
| Operating Junction and Storage Temperature                        | $T_J, T_{STG}$ | -55 to 150                    | $^\circ\text{C}$ |
| Source Current (Body Diode)                                       | $I_S$          | 350                           | mA               |
| Lead Temperature for Soldering Purposes (1/8" from case for 10 s) | $T_L$          | 260                           | $^\circ\text{C}$ |


## THERMAL RESISTANCE RATINGS

| Parameter                                          | Symbol          | Max | Unit               |
|----------------------------------------------------|-----------------|-----|--------------------|
| Junction-to-Ambient – Steady State (Note 1)        | $R_{\theta JA}$ | 500 | $^\circ\text{C/W}$ |
| Junction-to-Ambient – $t \leq 5\text{ s}$ (Note 1) |                 | 447 |                    |


Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Surface mounted on FR4 board using 1 in sq pad size (Cu. area = 1.127 in sq [1 oz] including traces).


| $V_{(BR)DS}$ | $R_{DS(on)}$ Typ       | $I_D$ Max (Note 1) |
|--------------|------------------------|--------------------|
| 20           | 400 m $\Omega$ @ 4.5 V | 540 mA             |
|              | 500 m $\Omega$ @ 2.5 V |                    |
|              | 700 m $\Omega$ @ 1.8 V |                    |



## MARKING DIAGRAM




SOT-563-6  
CASE 463A



TV = Specific Device Code  
M = Date Code  
■ = Pb-Free Package

(Note: Microdot may be in either location)

## PINOUT: SOT-563



## ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 4 of this data sheet.

NOTE: Some of the devices on this data sheet have been **DISCONTINUED**. Please refer to the table on page 4.

# NTZD3154N

## ELECTRICAL CHARACTERISTICS ( $T_J = 25\text{ }^{\circ}\text{C}$ unless otherwise noted.)

| Parameter                                                 | Symbol            | Test Condition                                      | Min                                 | Typ | Max       | Unit          |               |
|-----------------------------------------------------------|-------------------|-----------------------------------------------------|-------------------------------------|-----|-----------|---------------|---------------|
| OFF CHARACTERISTICS                                       |                   |                                                     |                                     |     |           |               |               |
| Drain-to-Source Breakdown Voltage                         | $V_{(BR)DSS}$     | $V_{GS} = 0\text{ V}, I_D = 250\text{ }\mu\text{A}$ | 20                                  | –   | –         | V             |               |
| Drain-to-Source Breakdown Voltage Temperature Coefficient | $V_{(BR)DSS}/T_J$ | –                                                   | –                                   | 14  | –         | mV/°C         |               |
| Zero Gate Voltage Drain Current                           | $I_{DSS}$         | $V_{GS} = 0\text{ V}$<br>$V_{DS} = 16\text{ V}$     | $T_J = 25\text{ }^{\circ}\text{C}$  | –   | –         | 1.0           | $\mu\text{A}$ |
|                                                           |                   |                                                     | $T_J = 125\text{ }^{\circ}\text{C}$ | –   | –         | 5.0           |               |
| Gate-to-Source Leakage Current                            | $I_{GSS}$         | $V_{DS} = 0\text{ V}, V_{GS} = \pm 4.5\text{ V}$    | –                                   | –   | $\pm 5.0$ | $\mu\text{A}$ |               |

## ON CHARACTERISTICS (Note 3)

|                                            |                  |                                                 |      |     |      |                        |
|--------------------------------------------|------------------|-------------------------------------------------|------|-----|------|------------------------|
| Gate Threshold Voltage                     | $V_{GS(TH)}$     | $V_{GS} = V_{DS}, I_D = 250\text{ }\mu\text{A}$ | 0.45 | –   | 1.0  | V                      |
| Negative Threshold Temperature Coefficient | $V_{GS(TH)}/T_J$ | –                                               | –    | 2.0 | –    | mV/ $^{\circ}\text{C}$ |
| Drain-to-Source On Resistance              | $R_{DS(on)}$     | $V_{GS} = 4.5\text{ V}, I_D = 540\text{ mA}$    | –    | 0.4 | 0.55 | $\Omega$               |
|                                            |                  | $V_{GS} = 2.5\text{ V}, I_D = 500\text{ mA}$    | –    | 0.5 | 0.7  |                        |
|                                            |                  | $V_{GS} = 1.8\text{ V}, I_D = 350\text{ mA}$    | –    | 0.7 | 0.9  |                        |
| Forward Transconductance                   | $g_{FS}$         | $V_{DS} = 10\text{ V}, I_D = 540\text{ mA}$     | –    | 1.0 | –    | S                      |

## CHARGES AND CAPACITANCES

|                              |              |                                                                    |   |      |     |    |
|------------------------------|--------------|--------------------------------------------------------------------|---|------|-----|----|
| Input Capacitance            | $C_{ISS}$    | $V_{GS} = 0\text{ V}, f = 1.0\text{ MHz}, V_{DS} = 16\text{ V}$    | – | 80   | 150 | pF |
| Output Capacitance           | $C_{OSS}$    |                                                                    | – | 13   | 25  |    |
| Reverse Transfer Capacitance | $C_{RSS}$    |                                                                    | – | 10   | 20  |    |
| Total Gate Charge            | $Q_{G(TOT)}$ | $V_{GS} = 4.5\text{ V}, V_{DS} = 10\text{ V}; I_D = 540\text{ mA}$ | – | 1.5  | 2.5 | nC |
| Threshold Gate Charge        | $Q_{G(TH)}$  |                                                                    | – | 0.1  | –   |    |
| Gate-to-Source Charge        | $Q_{GS}$     |                                                                    | – | 0.2  | –   |    |
| Gate-to-Drain Charge         | $Q_{GD}$     |                                                                    | – | 0.35 | –   |    |

## SWITCHING CHARACTERISTICS, $V_{GS} = V$ (Note 4)

|                     |              |                                                                                                 |   |     |   |    |
|---------------------|--------------|-------------------------------------------------------------------------------------------------|---|-----|---|----|
| Turn-On Delay Time  | $t_{d(ON)}$  | $V_{GS} = 4.5\text{ V}, V_{DD} = 10\text{ V}, I_D = 540\text{ mA},$<br>$R_G = 10\text{ }\Omega$ | – | 6.0 | – | ns |
| Rise Time           | $t_r$        |                                                                                                 | – | 4.0 | – |    |
| Turn-Off Delay Time | $t_{d(OFF)}$ |                                                                                                 | – | 16  | – |    |
| Fall Time           | $t_f$        |                                                                                                 | – | 8.0 | – |    |

## DRAIN-SOURCE DIODE CHARACTERISTICS

|                       |          |                                                                                   |                                     |     |     |     |   |
|-----------------------|----------|-----------------------------------------------------------------------------------|-------------------------------------|-----|-----|-----|---|
| Forward Diode Voltage | $V_{SD}$ | $V_{GS} = 0\text{ V},$<br>$I_S = 350\text{ mA}$                                   | $T_J = 25\text{ }^{\circ}\text{C}$  | –   | 0.7 | 1.2 | V |
|                       |          |                                                                                   | $T_J = 125\text{ }^{\circ}\text{C}$ | –   | 0.6 | –   |   |
| Reverse Recovery Time | $t_{RR}$ | $V_{GS} = 0\text{ V}, dI_{SD}/dt = 100\text{ A}/\mu\text{s}, I_S = 350\text{ mA}$ | –                                   | 6.5 | –   | ns  |   |

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

- Surface-mounted on FR4 board using 1 in. sq. pad size (Cu. area = 1.127 in sq [1 oz] including traces).
- Pulse Test: pulse width  $\leq 300\text{ }\mu\text{s}$ , duty cycle  $\leq 2\%$ .
- Switching characteristics are independent of operating junction temperatures.



**TYPICAL PERFORMANCE CURVES** ( $T_J = 25^\circ\text{C}$  unless otherwise noted)




**Figure 1. On-Region Characteristics**




**Figure 2. Transfer Characteristics**




**Figure 3. On-Resistance versus Gate-to-Source Voltage**




**Figure 4. On-Resistance versus Drain Current and Gate Voltage**




**Figure 5. On-Resistance Variation with Temperature**




**Figure 6. Drain-to-Source Leakage Current versus Voltage**

TYPICAL PERFORMANCE CURVES ( $T_J = 25^\circ\text{C}$  unless otherwise noted)




Figure 7. Capacitance Variation




Figure 8. Gate-to-Source and Drain-to-Source Voltage versus Total Charge




Figure 9. Resistive Switching Time Variation versus Gate Resistance




Figure 10. Diode Forward Voltage versus Current

ORDERING INFORMATION

| Device           | Package              | Shipping           |
|------------------|----------------------|--------------------|
| NTZD3154NT1G     | SOT-563<br>(Pb-Free) | 4000 / Tape & Reel |
| NTZD3154NT1G-M07 |                      |                    |
| NTZD3154NT2G     |                      |                    |

DISCONTINUED (Note 5)

|              |                      |                    |
|--------------|----------------------|--------------------|
| NTZD3154NT1H | SOT-563<br>(Pb-Free) | 4000 / Tape & Reel |
| NTZD3154NT2H |                      |                    |
| NTZD3154NT5G |                      | 8000 / Tape & Reel |
| NTZD3154NT5H |                      |                    |

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

5. **DISCONTINUED:** These devices are not available. Please contact your **onsemi** representative for information. The most current information on these devices may be available on [www.onsemi.com](http://www.onsemi.com).

## NTZD3154N

### REVISION HISTORY

| Revision | Description of Changes                                                                                                                              | Date     |
|----------|-----------------------------------------------------------------------------------------------------------------------------------------------------|----------|
| 5        | NTZD3154NT1H, NTZD3154NT2H, and NTZD3154NT5H OPNs marked as discontinued.<br>Aligned the ORDERING INFORMATION table with data on the product pages. | 8/6/2026 |

This document has undergone updates prior to the inclusion of this revision history table. The changes tracked here only reflect updates made on the noted approval dates.







**SOT-563-6 1.60x1.20x0.55, 0.50P**  
**CASE 463A**  
**ISSUE J**


DATE 15 FEB 2024

NOTES:

1. DIMENSIONING AND TOLERANCING CONFORM TO ASME Y14.5-2018.
2. ALL DIMENSION ARE IN MILLIMETERS.
3. MAXIMUM LEAD THICKNESS INCLUDES LEAD FINISH THICKNESS. MINIMUM LEAD THICKNESS IS THE MINIMUM THICKNESS OF BASE MATERIAL.



| DIM | MILLIMETERS |      |      |
|-----|-------------|------|------|
|     | MIN.        | NOM. | MAX. |
| A   | 0.50        | 0.55 | 0.60 |
| b   | 0.17        | 0.22 | 0.27 |
| c   | 0.08        | 0.13 | 0.18 |
| D   | 1.50        | 1.60 | 1.70 |
| E   | 1.10        | 1.20 | 1.30 |
| e   | 0.50 BSC    |      |      |
| H   | 1.50        | 1.60 | 1.70 |
| L   | 0.10        | 0.20 | 0.30 |



RECOMMENDED MOUNTING FOOTPRINT\*

\* FOR ADDITIONAL INFORMATION ON OUR Pb-FREE STRATEGY AND SOLDERING DETAILS, PLEASE DOWNLOAD THE ON SEMICONDUCTOR SOLDERING AND MOUNTING TECHNIQUES REFERENCE MANUAL, SOLDERM/D.

STYLE 1:  
PIN 1. EMITTER 1  
2. BASE 1  
3. COLLECTOR 2  
4. EMITTER 2  
5. BASE 2  
6. COLLECTOR 1

STYLE 2:  
PIN 1. EMITTER 1  
2. EMITTER 2  
3. BASE 2  
4. COLLECTOR 2  
5. BASE 1  
6. COLLECTOR 1

STYLE 3:  
PIN 1. CATHODE 1  
2. CATHODE 1  
3. ANODE/ANODE 2  
4. CATHODE 2  
5. CATHODE 2  
6. ANODE/ANODE 1

STYLE 4:  
PIN 1. COLLECTOR  
2. COLLECTOR  
3. BASE  
4. EMITTER  
5. COLLECTOR  
6. COLLECTOR

STYLE 5:  
PIN 1. CATHODE  
2. CATHODE  
3. ANODE  
4. ANODE  
5. CATHODE  
6. CATHODE

STYLE 6:  
PIN 1. CATHODE  
2. ANODE  
3. CATHODE  
4. CATHODE  
5. CATHODE  
6. CATHODE

STYLE 7:  
PIN 1. CATHODE  
2. ANODE  
3. CATHODE  
4. CATHODE  
5. ANODE  
6. CATHODE


STYLE 8:  
PIN 1. DRAIN  
2. DRAIN  
3. GATE  
4. SOURCE  
5. DRAIN  
6. DRAIN

STYLE 9:  
PIN 1. SOURCE 1  
2. GATE 1  
3. DRAIN 2  
4. SOURCE 2  
5. GATE 2  
6. DRAIN 1

STYLE 10:  
PIN 1. CATHODE 1  
2. N/C  
3. CATHODE 2  
4. ANODE 2  
5. N/C  
6. ANODE 1

STYLE 11:  
PIN 1. EMITTER 2  
2. BASE 2  
3. COLLECTOR 1  
4. EMITTER 1  
5. BASE 1  
6. COLLECTOR 2

**GENERIC  
MARKING DIAGRAM\***



XX = Specific Device Code  
M = Month Code  
▪ = Pb-Free Package

\*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "▪", may or may not be present. Some products may not follow the Generic Marking.

|                         |                                        |                                                                                                                                                                                  |
|-------------------------|----------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>DOCUMENT NUMBER:</b> | <b>98AON11126D</b>                     | Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |
| <b>DESCRIPTION:</b>     | <b>SOT-563-6 1.60x1.20x0.55, 0.50P</b> | <b>PAGE 1 OF 1</b>                                                                                                                                                               |

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

**onsemi**, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## ADDITIONAL INFORMATION

### TECHNICAL PUBLICATIONS:

Technical Library: [www.onsemi.com/design/resources/technical-documentation](http://www.onsemi.com/design/resources/technical-documentation)  
onsemi Website: [www.onsemi.com](http://www.onsemi.com)

### ONLINE SUPPORT: [www.onsemi.com/support](http://www.onsemi.com/support)

For additional information, please contact your local Sales Representative at  
[www.onsemi.com/support/sales](http://www.onsemi.com/support/sales)

