Welcome to TE.com, you are viewing information for visitors in United States
CHOOSE ANOTHER SITE
STAY ON THIS SITE

2825082-2

CLUSTER BLOCK HSG_V0-GWT







TE Internal #: **2825082-2**
TE Internal Description: **CLUSTER BLOCK HSG_V0-GWT**

Product Type : **Terminal Housing**
Number of Circuits : **3**
Material : **PBT**
Connector Style : **Receptacle**
Sealable : **No**

Similar Products | Digital Datasheet

Compatible Parts & Tooling

We are here to help!
Get in touch with our product experts.

CHAT WITH US
EMAIL US
CALL US

Feedback

Documents | Features | Product Compliance

Product Drawings

CLUSTER BLOCK HSG_V0-GWT
CLUSTER BLOCK HSG_V0-GWT English

CAD Files

3D PDF
3D_CVM_CVM_2825082-2_A.pdf 3D

Customer View Model
ENG_CVM_CVM_2825082-2_A.2d_dxf.zip
English

ENG_CVM_CVM_2825082-2_A.3d_igs.zip
English

ENG_CVM_CVM_2825082-2_A.3d_stp.zip
English

Datasheets & Catalog Pages

Economy Cluster Blocks Flyer
ENG_DS_1-1773869-3_Economy_Cluster_Blocks_Flyer_1115.pdf English

Product Specifications

Application Specification
ENG_SS_114-5235_E.pdf English

Product Specification
ENG_SS_108-5205_E.pdf English

Agency Approvals

UL Report
ENG_AAD_UL_E28476_19770301_F.pdf English

Downloaded from Arrow.com.

Please review product documents or contact us for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features	Product Type : **Terminal Housing** Connector Style : **Receptacle** Sealable : **No** Wire/Cable Type : **Magnet Wire**
Configuration Features	Number of Circuits : **3** Number of Positions : **3**
Body Features	Material : **PBT** Color : **Black**
Contact Features	Accepts Terminal Style : **Receptacle** Pin Diameter : **2.29 mm [.09 in]**
Usage Conditions	Operating Temperature Range : **-20 – 120 °C [-4 – 248 °F]**
Industry Standards	UL Flammability Rating : **UL 94V-0**
EU RoHS Directive 2011/65/EU	*This declaration covers EU Directive 2011/65/EU incl. Delegated Directive 2015/863/EU. The restrictions under 2015/863/EU apply as of 22 July 2021 for EEE categories 8 (medical devices) and 9 (monitoring and control equipment).*
EU ELV Directive 2000/53/EC	
China RoHS 2 Directive MIIT Order No 32, 2016	
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: **JUL 2019 (201)** Candidate List Declared Against: **JUL 2017 (174)**
Halogen Content	
Solder Process Capability	Not reviewed for solder process capability

Downloaded from Arrow.com.

Compliance	
Compliance Documents	There may be Environmental Compliance related documents on the DOCUMENTATION Tab
Disclaimer	This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles'(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Products with Similar Specs

View All Similar Products

THIS PRODUCT **TOP RESULTS**

CLUSTER BLOCKS
2825082-2
CLUSTER BLOCK HSG_V0-GWT



CLUSTER BLOCKS
2825082-1
CLUSTER BLOCK HSG PBT




In-Stock

CLUSTER BLOCKS
1380145-2
CLUSTER BLOCK HSG .090 DIA



Non-Stocked

CLUSTER BLOCKS
1217263-1
HSG .090 CLUSTER BLOCK NAT



Non-Stocked

Downloaded from Arrow.com.

Product Type : **Terminal Housing**
Number of Circuits : **3**
Material : **PBT**
Connector Style : **Receptacle**
Sealable : **No**

Product Type : **Terminal Housing**
Number of Circuits : **3**
Material : **PBT**
Connector Style : **Receptacle**
Sealable : **No**

Product Type : **Terminal Housing**
Number of Circuits : **3**
Material : **PBT**
Connector Style : **Receptacle**
Sealable : **No**

Product Type : **Terminal Housing**
Number of Circuits : **3**
Material : **PBT**
Connector Style : **Receptacle**
Sealable : **No**

Downloaded from Arrow.com.