

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0348033211

Status:

Active

Overview:

Stac64 Single, Multi-Pocket and Hybrid Header System

Description:

CTX64 Female Terminal, Tin, S-Grip, D-Wind, Left Payoff, SAE 22

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Brochure (PDF)

General

Product Family

Series

Application

Crimp Quality Equipment

Overview

Product Name

UPC

Crimp Terminals

34803

Signal, Wire-to-Board

Yes

Stac64 Single, Multi-Pocket and Hybrid Header System

CTX64

887191519272

Physical

Gender

Grip Code

Material - Metal

Material - Plating Mating

Material - Plating Termination

Net Weight

Packaging Type

Termination Interface: Style

Wire Insulation Diameter

Wire Size AWG

Wire Size mm²

Female

S

Copper Alloy

Tin

Tin

0.114/g

Reel

Crimp or Compression

1.10 to 1.65mm

22

0.22-0.35

Electrical

Current - Maximum per Contact

Voltage - Maximum

See Receptacle Product Spec.

14V DC

Material Info



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2020)4578-DC (25 June 2020)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Compliant

RoHS Phthalates

Not Contained

Search Parts in this Series

34803 Series

Use With

34729 2.54mm Pitch Stac64 Right Angle Receptacle

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	Product #
Description	
Hand Crimp Tool for CTX64 Receptacle Terminal, 0.22, 0.30, 0.35mm² and 22 AWG	638193700
FineAdjust Applicator for CTX64 Mat Seal Receptacle Terminals, for Wire Process Use Only	639032600

This document was generated on 10/30/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION