



GC2626CT, Mechanical Grounding Connector, One to Two Cables to Bar

By Burndy
Catalog # [GC2626CT](#)



Cast Copper Alloy Mechanical Grounding Cable Tray Clamp, #2 Sol-2/0 Str. Al/Cu Rated, 3/8" Stud, Galvanized Steel Hardware, Tin-plated Connector

Application

For Direct Burial Applications In Concrete Or Earth And For Used With Aluminum Or Galvanized Steel Cable Tray

General

Catalog Number	GC2626CT
EU RoHS Indicator	Yes
Installation Torque	240 LBS/in
Recommended in-lb	
Material	Copper Alloy
Sub Brand	MECHANICAL CONNECTOR
Type	GC-CT
UPC	781810220573
UPC 14 Digit GTIN	00781810220573

Dimensions

Dimension - Cross Flats inch	0.56 in
Dimension - Height inch	1.95 in
Dimension - Height mm	49.5 mm
Dimension - Width inch	1.70 in
Dimension - Width mm	43 mm

Conductor Related

Conductor - AL Str Size	2 AWG;1 AWG;1/0 AWG;2/0 AWG
Conductor - AL Str Size Range	2 AWG-2/0 AWG
Conductor - Copper Solid Size	2 AWG;1 AWG;1/0 AWG;2/0 AWG
Conductor - Copper Solid Size Range	2 AWG-2/0 AWG
Conductor - Copper Str Size Range	2 AWG-2/0 AWG

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Carton Quantity	50
Minimum Pack Quantity	1

Product Assets

[360 Product View - BURN_GC2626CT](#)
[3D Models - GC2626CT_MODEL-STEP](#)
[3D Models - GC2626CT_MODEL-PDF](#)
[3D Models - GC2626CT_MODEL-IGES](#)
[3D Product View - BURN_GC2626CT](#)
[Catalogs - Burndy Grounding Catalog](#)
[Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_GCCT_LineArt_BW](#)
[Sales Drawings - sc082752-01](#)
[Sell Sheets - Type GC-CT Cable Tray Ground Clamp](#)
[Specifications - GC2626CT](#)



A Hubbell brand