

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Primary-switched TRIO POWER power supply for DIN rail mounting, input: 1-phase, output: 12 V DC/5 A

Product description

TRIO POWER power supplies with standard functionality  
TRIO POWER is particularly suited to standard machine production, thanks to 1- and 3-phase versions up to 960 W. The wide-range input and the international approval package enable worldwide use.  
The robust metal housing, the high electric strength, and the wide temperature range ensure a high level of power supply reliability.

Your advantages

- Use the third negative terminal block as a grounding terminal block and minimize installation costs
- Rugged design with metal housing and wide temperature range from -25 to +70°C
- Maximum operational reliability thanks to high MTBF (mean time between failures) of more than 500,000 hours and high dielectric strength of up to 300 V AC
- Compensation of voltage drops by means of output voltage that can be adjusted on the front

Commercial data

|                                      |                     |
|--------------------------------------|---------------------|
| Item number                          | 2866475             |
| Packing unit                         | 1 pc                |
| Minimum order quantity               | 1 pc                |
| Sales key                            | CM11                |
| Product key                          | CMPT12              |
| Catalog page                         | Page 172 (C-6-2015) |
| GTIN                                 | 4046356153751       |
| Weight per piece (including packing) | 638.4 g             |
| Weight per piece (excluding packing) | 500 g               |
| Customs tariff number                | 85044095            |
| Country of origin                    | CN                  |

# TRIO-PS/ 1AC/12DC/ 5 - Power supply unit



2866475

<https://www.phoenixcontact.com/us/products/2866475>

## Technical data

### Input data

|                                          |                                                             |
|------------------------------------------|-------------------------------------------------------------|
| Nominal input voltage range              | 100 V AC ... 240 V AC                                       |
| Input voltage range                      | 85 V AC ... 264 V AC (derating < 90 V AC: 2.5 % per Kelvin) |
| Derating                                 | < 90 V AC (2.5 %/V)                                         |
| Input voltage range AC                   | 85 V AC ... 264 V AC (derating < 90 V AC: 2.5 % per Kelvin) |
| Electric strength, max.                  | 300 V AC                                                    |
| Voltage type of supply voltage           | AC                                                          |
| Inrush current                           | < 15 A                                                      |
| Inrush current integral ( $I^2t$ )       | < 0.5 A <sup>2</sup> s                                      |
| AC frequency range                       | 45 Hz ... 65 Hz                                             |
| Mains buffering time                     | > 26 ms (120 V AC)<br>> 100 ms (230 V AC)                   |
| Current consumption                      | 1.1 A (100 V AC)<br>0.5 A (240 V AC)                        |
| Nominal power consumption                | 112.5 VA                                                    |
| Protective circuit                       | Transient surge protection; Varistor                        |
| Power factor (cos phi)                   | 0.64                                                        |
| Typical response time                    | < 1 s                                                       |
| Permissible backup fuse                  | B6 B10 B16                                                  |
| Recommended breaker for input protection | 6 A ... 16 A (Characteristics B, C, D, K)                   |
| Discharge current to PE                  | < 3.5 mA                                                    |

### Output data

|                                                    |                                                                                                                                               |
|----------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------|
| Efficiency                                         | > 83 % (for 230 V AC and nominal values)                                                                                                      |
| Output characteristic                              | U/I                                                                                                                                           |
| Nominal output voltage                             | 12 V DC $\pm$ 1 %                                                                                                                             |
| Setting range of the output voltage ( $U_{Set}$ )  | 10 V DC ... 18 V DC (> 12 V DC, constant capacity restricted)                                                                                 |
| Nominal output current ( $I_N$ )                   | 5 A (-25 °C ... 55 °C)                                                                                                                        |
| Derating                                           | 55 °C ... 70 °C (2.5 %/K)                                                                                                                     |
| Feedback voltage resistance                        | 25 V DC                                                                                                                                       |
| Protection against overvoltage at the output (OVP) | < 25 V DC                                                                                                                                     |
| Max. capacitive load                               | unlimited                                                                                                                                     |
| Active current limitation                          | Approx. 5.9 A (in the event of a short-circuit)                                                                                               |
| Control deviation                                  | < 1 % (change in load, static 10 % ... 90 %)<br>< 2 % (change in load, dynamic 10 % ... 90 %)<br>< 0.1 % (change in input voltage $\pm$ 10 %) |
| Residual ripple                                    | < 20 mV <sub>PP</sub>                                                                                                                         |
| Output power                                       | 60 W                                                                                                                                          |
| Peak switching voltages nominal load               | < 100 mV <sub>PP</sub>                                                                                                                        |
| Maximum no-load power dissipation                  | 0.9 W                                                                                                                                         |
| Power loss nominal load max.                       | 11 W                                                                                                                                          |

# TRIO-PS/ 1AC/12DC/ 5 - Power supply unit



2866475

<https://www.phoenixcontact.com/us/products/2866475>

|                        |                                            |
|------------------------|--------------------------------------------|
| Rise time              | < 2 ms ( $U_{OUT}$ (10 % ... 90 %))        |
| Connection in parallel | yes, for redundancy and increased capacity |
| Connection in series   | yes                                        |

## Connection data

### Input

|                                       |                     |
|---------------------------------------|---------------------|
| Connection method                     | Screw connection    |
| Conductor cross section, rigid min.   | 0.2 mm <sup>2</sup> |
| Conductor cross section, rigid max.   | 2.5 mm <sup>2</sup> |
| Conductor cross section flexible min. | 0.2 mm <sup>2</sup> |
| Conductor cross section flexible max. | 2.5 mm <sup>2</sup> |
| Conductor cross section AWG min.      | 24                  |
| Conductor cross section AWG max.      | 14                  |
| Stripping length                      | 9 mm                |
| Screw thread                          | M2,5                |
| Tightening torque, min                | 0.4 Nm              |
| Tightening torque max                 | 0.5 Nm              |

### Output

|                                       |                     |
|---------------------------------------|---------------------|
| Connection method                     | Screw connection    |
| Conductor cross section, rigid min.   | 0.2 mm <sup>2</sup> |
| Conductor cross section, rigid max.   | 2.5 mm <sup>2</sup> |
| Conductor cross section flexible min. | 0.2 mm <sup>2</sup> |
| Conductor cross section flexible max. | 2.5 mm <sup>2</sup> |
| Conductor cross section AWG min.      | 24                  |
| Conductor cross section AWG max.      | 14                  |
| Stripping length                      | 9 mm                |
| Screw thread                          | M2,5                |
| Tightening torque, min                | 0.4 Nm              |
| Tightening torque max                 | 0.5 Nm              |

## Signaling

|                           |           |
|---------------------------|-----------|
| Types of signaling        | LED       |
| Operating voltage display | Green LED |

### Signal output

|                        |                                           |
|------------------------|-------------------------------------------|
| Status display         | "DC OK" LED green                         |
| Note on status display | $U_{OUT} < 0.9 \times U_N$ : LED flashing |

## Electrical properties

|                                 |                        |
|---------------------------------|------------------------|
| Insulation voltage input/output | 4 kV AC (type test)    |
|                                 | 2 kV AC (routine test) |
| Insulation voltage output / PE  | 500 V DC (type test)   |
| Insulation voltage input / PE   | 2 kV AC (type test)    |
|                                 | 2 kV AC (routine test) |

# TRIO-PS/ 1AC/12DC/ 5 - Power supply unit



2866475

<https://www.phoenixcontact.com/us/products/2866475>

## Product properties

|                            |                     |
|----------------------------|---------------------|
| Product type               | Power supply        |
| Product family             | TRIO POWER          |
| MTBF (IEC 61709, SN 29500) | > 1853000 h (40 °C) |

## Insulation characteristics

|                      |                        |
|----------------------|------------------------|
| Protection class     | I (with PE connection) |
| Overvoltage category | III                    |
| Degree of pollution  | 2                      |

## Dimensions

|        |        |
|--------|--------|
| Width  | 32 mm  |
| Height | 130 mm |
| Depth  | 115 mm |

## Installation dimensions

|                                  |               |
|----------------------------------|---------------|
| Installation distance right/left | 0 mm / 0 mm   |
| Installation distance top/bottom | 50 mm / 50 mm |

## Mounting

|                         |                                                |
|-------------------------|------------------------------------------------|
| Mounting type           | DIN rail mounting                              |
| Assembly note           | alignable: horizontally 0 mm, vertically 50 mm |
| Mounting position       | horizontal DIN rail NS 35, EN 60715            |
| With protective coating | No                                             |

## Material specifications

|                      |                          |
|----------------------|--------------------------|
| Housing material     | Metal                    |
| Type of housing      | Steel sheet, zinc-plated |
| Side element version | Aluminum                 |

## Environmental and real-life conditions

### Ambient conditions

|                                                |                                                                                                 |
|------------------------------------------------|-------------------------------------------------------------------------------------------------|
| Degree of protection                           | IP20                                                                                            |
| Ambient temperature (operation)                | -25 °C ... 70 °C (> 55° C derating : 2.5%/K)                                                    |
| Ambient temperature (storage/transport)        | -40 °C ... 85 °C                                                                                |
| Climatic class                                 | 3K3 (in acc. with EN 60721)                                                                     |
| Max. permissible relative humidity (operation) | 95 % (at 25 °C, non-condensing)                                                                 |
| Shock                                          | 15g in all directions in acc. with IEC 60068-2-27                                               |
| Vibration (operation)                          | < 15 Hz, amplitude $\pm 2.5$ mm (according to IEC 60068-2-6)<br>15 Hz ... 150 Hz, 2.3g, 90 min. |

## Standards and regulations

|                                                                                                                                  |                          |
|----------------------------------------------------------------------------------------------------------------------------------|--------------------------|
| Rail applications                                                                                                                | EN 50121-4               |
| Standard – Electronic equipment for use in electrical power installations and their assembly into electrical power installations | EN 50178/VDE 0160 (PELV) |

# TRIO-PS/ 1AC/12DC/ 5 - Power supply unit



2866475

<https://www.phoenixcontact.com/us/products/2866475>

|                                                                                                                    |                            |
|--------------------------------------------------------------------------------------------------------------------|----------------------------|
| Standard – Limitation of mains harmonic currents                                                                   | EN 61000-3-2               |
| Standard - Electrical safety                                                                                       | EN 60950-1/VDE 0805 (SELV) |
|                                                                                                                    | EN 61558-2-17              |
| Standard – Protection against shock currents, basic requirements for protective separation in electrical equipment | EN 50178                   |
| Standard – Safety extra-low voltage                                                                                | EN 60950-1 (SELV)          |
|                                                                                                                    | EN 60204 (PELV)            |
| Standard - Safe isolation                                                                                          | DIN VDE 0100-410           |

## Approvals

|              |                               |
|--------------|-------------------------------|
| UL approvals | UL/C-UL listed UL 508         |
|              | UL/C-UL Recognized UL 60950-1 |

## Conformity/Approvals

|                                  |   |
|----------------------------------|---|
| SIL in accordance with IEC 61508 | 0 |
|----------------------------------|---|

## EMC data

|                                     |                                                   |
|-------------------------------------|---------------------------------------------------|
| Low Voltage Directive               | Conformance with Low Voltage Directive 2014/35/EC |
| EMC requirements for noise emission | EN 61000-6-3                                      |
|                                     | EN 61000-6-4                                      |
| EMC requirements for noise immunity | EN 61000-6-1                                      |
|                                     | EN 61000-6-2                                      |
| Electromagnetic compatibility       | Conformance with EMC Directive 2014/30/EU         |

## Electrostatic discharge

|                       |              |
|-----------------------|--------------|
| Standards/regulations | EN 61000-4-2 |
|-----------------------|--------------|

## Electrostatic discharge

|                   |                     |
|-------------------|---------------------|
| Contact discharge | 8 kV (Test Level 4) |
| Discharge in air  | 8 kV (Test Level 3) |
| Comments          | Criterion A         |

## Electromagnetic HF field

|                       |              |
|-----------------------|--------------|
| Standards/regulations | EN 61000-4-3 |
|-----------------------|--------------|

## Electromagnetic HF field

|                     |                  |
|---------------------|------------------|
| Frequency range     | 80 MHz ... 1 GHz |
| Test field strength | 10 V/m           |
| Frequency range     | 1 GHz ... 2 GHz  |
| Test field strength | 10 V/m           |
| Frequency range     | 2 GHz ... 3 GHz  |
| Test field strength | 10 V/m           |
| Comments            | Criterion A      |

## Fast transients (burst)

|                       |              |
|-----------------------|--------------|
| Standards/regulations | EN 61000-4-4 |
|-----------------------|--------------|

## Fast transients (burst)

# TRIO-PS/ 1AC/12DC/ 5 - Power supply unit



2866475

<https://www.phoenixcontact.com/us/products/2866475>

|          |                                    |
|----------|------------------------------------|
| Input    | 4 kV (Test Level 4 - asymmetrical) |
| Output   | 4 kV (Test Level 4 - asymmetrical) |
| Signal   | 2 kV (Test Level 3 - asymmetrical) |
| Comments | Criterion A                        |

## Surge voltage load (surge)

|                       |              |
|-----------------------|--------------|
| Standards/regulations | EN 61000-4-5 |
|-----------------------|--------------|

## Surge voltage load (surge)

|          |                                      |
|----------|--------------------------------------|
| Input    | 1 kV (Test Level 2 - symmetrical)    |
|          | 2 kV (Test Level 3 - asymmetrical)   |
| Output   | 0.5 kV (Test Level 1 - symmetrical)  |
|          | 0.5 kV (Test Level 1 - asymmetrical) |
| Comments | Criterion B                          |

## Conducted interference

|                       |              |
|-----------------------|--------------|
| Standards/regulations | EN 61000-4-6 |
|-----------------------|--------------|

## Conducted interference

|                 |                     |
|-----------------|---------------------|
| Frequency range | 0.15 MHz ... 80 MHz |
| Comments        | Criterion A         |
| Voltage         | 10 V (Test Level 3) |

## Voltage dips

|                       |               |
|-----------------------|---------------|
| Standards/regulations | EN 61000-4-11 |
|-----------------------|---------------|

## Emitted interference

|                                                  |                                                                            |
|--------------------------------------------------|----------------------------------------------------------------------------|
| Standards/regulations                            | EN 61000-6-3                                                               |
| Radio interference voltage in acc. with EN 55011 | EN 55011 (EN 55022) Class B, area of application: Industry and residential |
| Emitted radio interference in acc. with EN 55011 | EN 55011 (EN 55022) Class B, area of application: Industry and residential |

# TRIO-PS/ 1AC/12DC/ 5 - Power supply unit




2866475

<https://www.phoenixcontact.com/us/products/2866475>

## Drawings

Block diagram



# TRIO-PS/ 1AC/12DC/ 5 - Power supply unit



2866475

<https://www.phoenixcontact.com/us/products/2866475>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2866475>



**cUL Recognized**  
Approval ID: FILE E 211944



**UL Recognized**  
Approval ID: FILE E 211944



**EAC**  
Approval ID: EAC-Zulassung



**EAC**  
Approval ID: RU S-DE.BL08.W.00764



**UL Listed**  
Approval ID: FILE E 123528



**cUL Listed**  
Approval ID: FILE E 123528



**EAC**  
Approval ID: RU S-DE.BL08.W.00764

**CoC / Compliance Statement**  
Approval ID: 16-198-00

**cULus Recognized**

**cULus Listed**



# TRIO-PS/ 1AC/12DC/ 5 - Power supply unit



2866475

<https://www.phoenixcontact.com/us/products/2866475>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-11.0 | 27040701 |
| ECLASS-12.0 | 27040701 |
| ECLASS-13.0 | 27040701 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002540 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121000 |
|-------------|----------|

# TRIO-PS/ 1AC/12DC/ 5 - Power supply unit



2866475

<https://www.phoenixcontact.com/us/products/2866475>

## Environmental product compliance

|                                         |                                                                                                                                                                                                                                   |
|-----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS                                 |                                                                                                                                                                                                                                   |
| Fulfills EU RoHS substance requirements | Yes                                                                                                                                                                                                                               |
| Exemption                               | 7(a), 7(c)-I                                                                                                                                                                                                                      |
| China RoHS                              |                                                                                                                                                                                                                                   |
| Environment friendly use period (EFUP)  | EFUP-25                                                                                                                                                                                                                           |
|                                         | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |
| EU REACH SVHC                           |                                                                                                                                                                                                                                   |
| REACH candidate substance (CAS No.)     | Lead(CAS: 7439-92-1)                                                                                                                                                                                                              |
| SCIP                                    | b85212f4-6940-4567-95cf-e0b95150b85b                                                                                                                                                                                              |

# TRIO-PS/ 1AC/12DC/ 5 - Power supply unit



2866475

<https://www.phoenixcontact.com/us/products/2866475>

## Accessories

### VIP-2/SC/PDM-2/24 - Potential distributors

2315269

<https://www.phoenixcontact.com/us/products/2315269>



VARIOFACE module, with two equipotential busbars (P1, P2) for potential distribution, for mounting on NS 35 rails. Module width: 70.4 mm

---

### VIP-3/PT/PDM-2/24 - Potential distributors

2903798

<https://www.phoenixcontact.com/us/products/2903798>



VARIOFACE module with push-in connection and two equipotential busbars (P1, P2) for potential distribution, for mounting on NS 35 rails. Module width: 57.1 mm

# TRIO-PS/ 1AC/12DC/ 5 - Power supply unit

2866475

<https://www.phoenixcontact.com/us/products/2866475>



## PLT-SEC-T3-230-FM-UT - Type 3 surge protection device

2907919

<https://www.phoenixcontact.com/us/products/2907919>



Type 2/3 surge protection, consisting of protective plug and base element with screw connection. For single-phase power supply network with integrated status indicator and remote signaling. Nominal voltage: 230 V AC/DC

---

## PLT-SEC-T3-24-FM-UT - Type 3 surge protection device

2907916

<https://www.phoenixcontact.com/us/products/2907916>



Type 3 surge protection, consisting of protective plug and base element, with integrated status indicator and remote signaling for single-phase power supply networks. Nominal voltage: 24 V AC/DC

---

Phoenix Contact 2024 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)