

## USB 2.0 A/B Cable (M/M), 15 ft. (4.57 m)

MODEL NUMBER: **U022-015**



Make the connection between a USB device and your computer's USB port. This USB 2.0 A/B Gold Device Cable assures that you get maximum performance from USB 2.0 devices (e.g. printers, external hard drives). It supports fast data transfer rates up to 480 Mbps, and is backward compatible with USB 1.1.

### Description

Tripp Lite's 15-ft. (4.57 m) gold USB 2.0 A/B device cable meets or exceeds USB 2.0 specifications. Connects a USB device to a USB port on a computer or hub. Backward compatible - can be used with older USB 1.1 applications as well. All Tripp Lite USB 2.0 cabling include superior foil shielding for reliable, error-free data communications. The significantly faster data transfer rates of USB 2.0 (up to 480 Mbps) make them perfect for multimedia applications. Features gold plated connectors and gold plated copper contacts for superior conductivity. The cable is manufactured with molded connectors and integral strain relief for extra durability and long life.

### Features

- Meets or exceeds USB 2.0 specifications
- Supports faster data transfer rate (1.5 to 480 Mbps) for low speed and high speed devices including multimedia applications
- Premium double-shielded cables with tinned copper braid and aluminum Mylar foil
- Gold-plated connectors and gold-plated copper contacts for superior conductivity.
- Molded connectors and integral strain relief for extra durability and long life.

## Specifications

| OVERVIEW |              |
|----------|--------------|
| UPC Code | 037332122988 |

### Highlights

- Meets or exceeds USB 2.0 specifications
- Supports faster data transfer rate (1.5 to 480 Mbps) for low speed and high speed devices, including multimedia applications
- Premium double-shielded cables with tinned copper braid and aluminum mylar foil feature twisted 28AWG data lines, and 24AWG power lines.
- Gold-plated connectors provide superior conductivity

### System Requirements

- Any USB device requiring a USB cable
- USB 2.0 performance only when used with USB 2.0 device and USB 2.0 controller

### Package Includes

- 15-ft. (4.57 m) USB 2.0 Gold Cable USB-A to USB-B



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

|                                     |                           |
|-------------------------------------|---------------------------|
| Technology                          | USB 2.0 (High Speed); USB |
| <b>PHYSICAL</b>                     |                           |
| Color                               | Black                     |
| Cable Length (ft.)                  | 15                        |
| Cable Length (m)                    | 4.6                       |
| Shipping Dimensions (hwd / cm)      | 22.86 x 17.78 x 1.27      |
| Shipping Dimensions (hwd / in.)     | 9.00 x 7.00 x 0.50        |
| Shipping Weight (kg)                | 0.15                      |
| Shipping Weight (lbs.)              | 0.34                      |
| <b>CONNECTIONS</b>                  |                           |
| Side A - Connector 1                | USB A (MALE)              |
| Side B - Connector 1                | USB B (MALE)              |
| <b>STANDARDS &amp; COMPLIANCE</b>   |                           |
| Certifications                      | RoHS-Compliant            |
| <b>WARRANTY</b>                     |                           |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>