




+ WIRE AND CABLE
HOOK UP WIRE



✓ Active

TE CONNECTIVITY (TE)
22759/33-26-0
Raychem | RC

22759/33-26-0
TE Internal Number: 216324-001
Mil-Spec: M22759/33-26-0
Alias ID: 5-1191576-4

EU RoHS Compliant
EU ELV Compliant

Cable Type Spec 55
Voltage Rating (V) 600
Insulation Material Radiation-Crosslinked, Modified ETFE
Conductor Material Silver-Coated High Strength Copper Alloy
Wire Size (AWG) 26

↓ **PRODUCT DRAWING**
English

DOCUMENTATION

Product Drawings

WIRE, RADIATION-CROSSLINKED, MODIFIED, ETFE-INSULATED, SILVER-COATED HIGH STRENGTH COPPER ALLOY, LIGHTWEIGHT

PDF (TIFF AVAILABLE)
English

Product Specifications

Product Specification

Wire And Cable, Electric, Radiation-Crosslinked, Extruded, Modified, Fluoropolymer-Insulated Copper Or Copper Alloy

PDF
English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

- Cable Type** Spec 55
- Cable Style** Primary
- Product Classification** Cable - High Performance - Spec 44, 55 & RCW
- Product Type** Cable

Configuration Features

- Number of Strands** 19
- Number of Conductors** 1

Electrical Characteristics

- Voltage Rating (V)** 600

Body Features

- Insulation Material** Radiation-Crosslinked, Modified ETFE
- Conductor Material** Silver-Coated High Strength Copper Alloy
- Wire Color** Black

Dimensions

- Strand Size (AWG)** 38
- Wire Size (AWG)** 26
- Wire Size (mm²)** .129
- Conductor Diameter** .5 mm [.02 in]
- Overall Outside Diameter** .81 mm [.032 in]
- Insulation Thickness (in)** .005
- Wire Diameter** .81 mm [.032 in]

Usage Conditions

- Operating Temperature Range (°C)** -65 – 200

Other

- Wire Source** United States

PRODUCT COMPLIANCE



Statement of Compliance

- Statement of Compliance**
- PDF

