



Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.

FCI

All rights strictly reserved. Reproduction or issue to third parties in any form without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NO.	ROW S	SIGNAL						POWER						
		E2	6	5	4	3	2	1	P5	P4	P3	P2	P1	E1
51752-018-- NOTE: 3	D C B A		E	E	E	E	E	E	PD	PD	PA	PD	PD	



CODE	DIM "M" MATING LENGTH		CONTACT TYPE
E	N/A	[N/A]	SIGNAL
PD	.092	[2.34]	POWER
HA	N/A	[N/A]	HOLD-DOWN
PA	.042	[1.07]	POWER

mat'l code SEE NOTE 2				tolerances unless otherwise specified		CUSTOMER COPY		www.fciconnect.com	
lfr	ecn no.	dr	date	linear	.XX±.01/0.X±0.3	projection 	INCH/MM scale 1:1	title 5P + 24S VERTICAL STB RECEPT	product family PwrBlade
A	DG06-0065	JMG	02/21/06		.XXX±.005/0.XX±0.13				
					.XXX±.0020/0.XXX±0.051				
				angles	0°±2°				
				dr	JM GUO 02/21/06				
				enqr	SLUO 02/21/06				
				chr	BEER FU 02/21/06				
				appd	JOSEPH HSIA 02/21/06				
sheet index	revision sheet	A 1	A 2	A 3	A 4				

cage code 22526




Pro/E


Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

FCI

PRODUCT NUMBER
51752-018__
NOTE: 3



mat'l code SEE NOTE 2				tolerances unless otherwise specified		CUSTOMER		 www.fciconnect.com	
lfr	ecn no.	dr	date	linear	.XX±.01/0.X±0.3 .XXX±.005/0.XX±0.13 .XXXX±.0020/0.XXX±0.051	COPY	projection		
A				angles	0°±2°			title	5P + 24S VERTICAL STB RECEPT
				dr	JM GUO 02/21/06	INCH/MM		product family	PwrBlade
				engr	SLUO 02/21/06	scale		size	dwg no
				chr	BEER FU 02/21/06	1:1		A	51752-018
				appd	JOSEPH HSIA 02/21/06				
sheet index	revision sheet								

cage code 22526

Pro/E

PDM: Rev:A

STATUS: Released

Printed: Dec 20, 2010

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.




PRODUCT NUMBER
51752-018--
NOTE: 3

1 | 2

3 |

4



mat'l code				tolerances unless otherwise specified		CUSTOMER		FCI			
lfr	ecn no.	dr	date	linear	.XX±.01/0.X±0.3	COPY		www.fciconnect.com			
A				linear	.XXX±.005/0.XX±0.13	projection		title 5P + 24S			
				angles	.XXX±.0020/0.XXX±0.051	INCH/MM		VERTICAL STB RECEPT			
				dr	JM GUO 02/21/06	scale		product family PwrBlade			
				enrg	SLUO 02/21/06	1:1		code 213			
				chr	BEER FU 02/21/06			size 51752-018			
				appd	JOSEPH HSIA 02/21/06			sheet 3 of 4			
sheet index	revision	sheet									

Pro/E

3 |

cage code 22526

4

PDM: Rev:A

STATUS: Released

Printed: Dec 20, 2010

PRODUCT NUMBER
51752-018__
NOTE: 3

NOTES:

1. DIMENSIONS AND TOLERANCES ARE IN ACCORDANCE WITH
ASME Y14.5M, 1994 UNLESS OTHERWISE SPECIFIED.

CONNECTOR NOTES:

2 HOUSING MATERIAL: UL 94 V-0 GLASS FILLED
HIGH-TEMP THERMOPLASTIC
POWER CONTACT MATERIAL: COPPER ALLOY
SIGNAL PIN MATERIAL: COPPER ALLOY

3. 51752-018;51752-018LF;51752-018GLF PLATING SPEC. SEE PRINT:10064183

4 MANUFACTURER'S NAME, P/N, AND DATE CODE TO APPEAR ON
THIS SURFACE.

5. PRODUCT SPECIFICATION GS-12-149.
APPLICATION SPECIFICATION BUS-20-067.

6. PACKAGED IN TRAYS.

PCB NOTES:
7. ALL HOLE DIAMETERS ARE FINISHED HOLE SIZE.

8 MOUNTING HOLES, WHERE APPLICABLE, ARE UNPLATED.

9 $\varnothing .0453 \pm .0010$ [1.151 $\pm$ 0.025] DRILLED HOLES PLATED WITH
.0003 [0.008] MIN SnPb OVER .001 [0.03]
TO .003 [0.08] Cu PLATING TO ACHIEVE
 $\varnothing .040 \pm .003$ [1.02 $\pm$.07] HOLE.

10 "DIM XXX" TO BE DETERMINED BY THE CUSTOMER.

11 CONNECTOR KEEP-OUT ZONE.

mat'l code				SEE NOTE 2		tolerances unless otherwise specified		CUSTOMER		A FCI www.fciconnect.com		
lfr	ecn no.	dr	date	linear	.XX $\pm$.01/0.X $\pm$ 0.3			COPY		title 5P + 24S VERTICAL STB RECEPT		
A					.XXX $\pm$.005/0.XX $\pm$ 0.13			projection				
					.XXXX $\pm$.0020/0.XXX $\pm$ 0.051							
				angles	0 $\pm$ 2°					product family PwrBlade		
				dr	JM GUO	02/21/06	INCH/MM		code			
				engr	SLUO	02/21/06			213			
				chr	BEER FU	02/21/06	scale 1:1		sheet			
				appd	JOSEPH HSIA	02/21/06			A		51752-018	4 of 4
sheet index		revision sheet										

code code 22526

Pro/E