
© 2017 TE Connectivity Ltd. family of companies. All Rights Reserved

WIRE AND CABLE

TWISTED PAIR CABLE



✔ Active

TE CONNECTIVITY (TE)

55A0121-22-9/90

Raychem | RC , SP

55A0121-22-9/90
TE Internal Number: 316117-000
Alias ID: 8-1192393-8

EU RoHS Compliant
EU ELV Compliant

Cable Type Spec 55

Voltage Rating (VAC) 600

Insulation Material Radiation-Crosslinked, Modified ETFE

Conductor Material Tin-Plated Copper

Wire Size (AWG) 22

PRODUCT DRAWING
English

DOCUMENTATION

Product Drawings

Two Conductor Cable, Unshielded, Unjacketed, General Purpose, 600 Volt
PDF
English

Product Specifications

Product Specification

Wire And Cable, Electric, Radiation-Crosslinked, Extruded, Modified, Fluoropolymer-Insulated Copper Or Copper Alloy
PDF
English

FEATURES

Downloaded from Arrow.com.

Please review product documents or contact us for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Cable Type Spec 55
Cable Style Primary
Product Type Cable
Product Classification Cable - High Performance - Spec 44, 55 and RCW

Configuration Features

Number of Strands 19
Number of Conductors 2

Electrical Characteristics

Voltage Rating (VAC) 600

Body Features

Insulation Material Radiation-Crosslinked, Modified ETFE
Conductor Material Tin-Plated Copper

Dimensions

Strand Size (AWG) 34
Wire Size (AWG) 22
Overall Outside Diameter 2.23 mm [.086 in]
Conductor Diameter .74 mm [.029 in]

Usage Conditions

Operating Temperature Range (°C) -65 – 150

PRODUCT COMPLIANCE

Statement of Compliance

Statement of Compliance
PDF

Downloaded from Arrow.com.