


208116-1 Product Details



208116-1

TE Part Number: 208116-1

Active

Add to Part List

View 3D PDF

5mm (.197") Centerline, 600 V, 14 A max. (Metrimate)

Not EU RoHS or ELV Compliant (Find RoHS Compliant Alternates)

Product Highlights:

- Header
- In-Line Connector Configuration
- Number of Positions = 6
- Pin
- Without Coaxial Socket

View all Features | Find Similar Products

Live Product Chat

Quick Links

- Check Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product
- Request Samples

NEW!

Documentation & Additional Information

Product Drawings: - HEADER ASSEMBLY, PIN, 6 POSITION, METRIMATE (PDF, English) Catalog Pages/Data Sheets: - None Available Product Specifications: - None Available Application Specifications: - Metrimate Self-Locking Connectors (PDF, English) - METRIMATE Self-Locking Connectors (PDF, English) Instruction Sheets: - None Available CAD Files: (CAD Format & Compression Information) 2D Drawing (DXF, Version G) 3D Model (IGES, Version G) 3D Model (STEP, Version G)	Additional Information: - Product Line Information Additional Product Images: - PCB Layout Related Products: - Tooling
List all Documents	

Product Features (Please use the Product Drawing for all design activity)

Product Type Features: - Product Type = Header - Number of Positions = 6 - Gender = Pin - Keyed = No - Mount = Printed Circuit Board - PCB Mount Angle = Right Angle - Mounting Ears = With - Post Type = Solder Post - Mating Connector Lock = Without - PCB Retention Feature = Yes Electrical Characteristics: - Voltage (VAC) = 600 - Current Rating (Amps.) = 14 Termination Related Features: - Termination (Solder) Post Length (mm [in]) = 3.05 [0.120] Body Related Features: - Connector Configuration = In-Line - Coaxial Socket = Without - Centerline (mm [in]) = 5.08 [0.200] - Jackscrew = Without 8/32 Insert = No - PCB Retention Method = Mounting Holes	Contact Related Features: - Contact Mating Area Plating Material = Tin-Lead over Copper - Contact Material = Copper Alloy Housing Related Features: - Housing Material = Thermoplastic - Housing Color = Red - Housing Flammability Rating = UL 94V-0 Industry Standards: - RoHS/ELV Compliance = Not ELV/RoHS compliant - Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C Other: - Brand = AMP
--	---