
CONFIGURATION CONTROL LEVEL: 3

PRODUCT DATA DRAWING

REVISION HISTORY			
REV	DESCRIPTION	DATE	APPROVED
-	NRN 45603	02/21	SEE PDM
A	DCN 51631	05/22	



MATERIAL:

CONNECTORS: 2.92mm FEMALE IP68 (1521-60189)
2.92mm MALE (SF1511-60071)

CABLE: T-FLEX 405 (200-70-139)

STRAIN RELIEF: M23053/5

PERFORMANCE:

IMPEDANCE: 50 OHMS
FREQ. RANGE: DC TO 38.0 GHz.

MATERIAL: PER BOM
FINISH: PER BOM

PROPRIETARY

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF SV MICROWAVE, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF SV MICROWAVE, INC IS PROHIBITED.

DIMENSIONS ARE IN INCHES TOLERANCES:

FRACTIONAL: ±1/64 ANGULAR: X° ±1°0'
X°X' ±15'

DECIMAL: .X ±.030
.XX ±.010
.XXX ±.005

INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994

THIRD ANGLE PROJECTION

UNLESS OTHERWISE SPECIFIED

1) ALL DIMENSIONS ARE AFTER PLATING.
2) BREAK CORNERS & EDGES .005 R. MAX.
3) CHAM. 1ST & LAST THREADS.
4) SURFACE ROUGHNESS 63 √ MIL-STD-10.
5) DIA.'S ON COMMON CENTERS TO BE CONCENTRIC WITHIN .005 T.I.R.
6) REMOVE ALL BURRS

DRAWN: JPM 02/11/21
CHECKED: SEE PDM
APPROVED: SEE PDM
E.M. SIMULATION: N/A

Amphenol SV MICROWAVE
www.svmicrowave.com

TITLE: 2.9MM STR. IP68 BLKHD F TO 2.9MM STR. M TFLEX 405 CABLE ASSEMBLY

SIZE B | DWG. NO. 7015-1074.PDD

SCALE: 4:1 | SHEET 1 OF 1

Downloaded from Arrow.com.