

NA132N, Substation - Copper Terminal, 1/2" Cu Pipe, 2-Hole

By Burndy
Catalog # [NA132N](#)

Copper Bolted Terminal , Tube to Flat , 1/2" Cu Pipe , 2 Pad Holes , 230 kV.



Features

- Type NA for Copper Tube to Pad
- High copper alloy terminal for joining copper tube to a flat pad
- Letter N on end of the catalog number indicates pad drilled to NEMA standards
- One-wrench installation

Application

Substation

Specifications

Standards - RoHS Compliance Status	EX
Certification - CSA Approved	No

Conductor

Number Of Conductors	1
Conductor - Connection Combination	Tube to Flat
Conductor Type	<ul style="list-style-type: none"> • CU Tube Std-Size • CU Tube EH-Size
Conductor - Copper Tube Std Size Range	1/2 IPS
Conductor - Copper Tube Std Size	1/2 IPS
Conductor - Copper Tube EH Size Range	1/2 IPS
Conductor - Copper Tube EH Size	1/2 IPS

Configuration

Physical Attribute - Pad Configuration	1.5 x 3 - 2 holes
Physical Attribute - Pad Alignment	Offset
Physical Attribute - Number of Holes	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.50 in
Package Height	0.000 in
Dimension - Height mm	44.5 mm
Dimension - Hole Size fraction	9/16
Dimension - Height inch	1.75 in
Dimension - Height fraction	1-3/4
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.75 in
Package Width	0.000 in
Dimension - L Length Overall mm	133 mm
Dimension - Width fraction	2-1/4 in
Dimension - Width mm	57 mm
Dimension - Width inch	2.25 in
Dimension - B Length inch	2.00 in
Dimension - D inch	3.00 in
Dimension - N inch	0.63 in
Dimension - Length Overall inch	5.25 in

General

Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
Plated	N
Clamping Element Design	Body and Cap
UPC	781810002308
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810002308
UPC 14 Digit GTIN	00781810002308

Logistics

Minimum Pack Quantity	3
Pallet Quantity	1
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)