

Part No. X9001248

External Magnetic Mount LTE Antenna

700 / 800 / 900 / 1800 / 2100 / 2600 MHz

Supports: LTE Cat 1, LTE-M, SigFox, LoRa, NB-IoT, M2M applications, 2G, 3G, Cellular



KYOCERA AVX family of external antennas are designed to offer the best performances for a wide range of applications. X9001248 is specially developed to deliver stable gain across 2G, 3G, and 4G cellular bands. This antenna is designed to be mounted on a ground plane for optimal performance.

Electrical Specifications

Typical Characteristics in Free Space and on 300 x 250 mm ground plane with 1meter cable

Frequency (MHz)	Free space		On 300 x 250 mm Ground Plane	
	698 - 960	1710 - 2690	698 - 960	1710 - 2690
Return Loss	< -5.2 dB	< -5.8 dB	< -5.2 dB	< -6.0 dB
Average Peak Gain	-0.5 dBi	-0.2dBi	1.8 dBi	1.9 dBi
Average Efficiency	33 %		54%	36%
Impedance	50 ohm			

Mechanical Specifications & Ordering Part Number

Ordering Part Number	X9001248
Dimensions (mm)	110.0 height 29.0 base diameter
Connector Types	SMA Male, RP-SMA Male
Weight (grams)	~50.0
Mounting	Magnetic
Color	Black
Cable/Length	LMR100 or RG-174/(Refer to pages 5-8)
Ingress Protection	IP65
Operating Temperature (°C)	-40 to + 70
Radome Material	TPE

External Magnetic Mount LTE Antenna

Low Band : 698 – 960 MHz

High Band : 1170 – 2690 MHz

KEY BENEFITS

Quicker Time-to-Market

Standard part means fewer design changes with, simple implementation

Easy Assembly using RP-SMA or SMA

Best in Class Performance

External antennas are designed to maintain high efficiency in a variety of device configurations

Great Flexibility

Standard connector to makes easy set-up

Environmental Compliance

Products are the latest RoHS version compliant.


APPLICATIONS

- Telematics
- Smart metering
- Home automation
- Smart city
- Structural health monitoring
- Predictive maintenance
- M2M devices


LTE Magnetic mount External antenna specifications
KYOCERA AVX produces a wide variety of standard and custom antennas to meet user needs

Return Loss, Efficiency and Peak Gain Plots

Typical performance measured in Free Space
on a 300x250mm ground plane with a 1meter cable




X9001248-4GMSMB1000R




X9001248-4GMSMB1000R


Low Band Return Loss




High Band Return Loss




Low Band Efficiency




High Band Efficiency



Low Band Peak Gain



High Band Peak Gain





LTE Magnetic mount External antenna specifications
KYOCERA AVX produces a wide variety of standard and custom antennas to meet user needs

Radiation Patterns Plots

Typical performance measured in Free Space
on a 300x250mm ground plane with a 1meter cable
Measured at 850, 900, 1850 and 2550 MHz

Free Space

X9001248-4GMSMB1000R




LTE Magnetic mount External antenna specifications
KYOCERA AVX produces a wide variety of standard and custom antennas to meet user needs






Radiation Patterns Plots

Typical performance measured in Free Space
on a 300x250mm ground plane with a 1meter cable
Measured at 850, 900, 1850 and 2550 MHz

On Ground Plane



Measured at 850,
900,1850 and 2550 MHz




LTE Magnetic mount External antenna specifications
KYOCERA AVX produces a wide variety of standard and custom antennas to meet user needs

Mechanical Specifications (SMA MALE, LMR100)

Typical antenna dimensions in mm.

Part Number	A	Ø	Cable Type	XXXX Cable Length	Z Cable Tolerance	Connector
X9001248-4GMSMBXXXXL	110±3.0	29±0.5	LMR100	0XXX < 150	± 3.0	SMA MALE
X9001248-4GMSMB0050L	110±3.0	29±0.5	LMR100	50	± 3.0	SMA MALE
X9001248-4GMSMB0100L	110±3.0	29±0.5	LMR100	100	± 3.0	SMA MALE
X9001248-4GMSMB0150L	110±3.0	29±0.5	LMR100	150	± 4.0	SMA MALE
X9001248-4GMSMB0200L	110±3.0	29±0.5	LMR100	200	± 4.0	SMA MALE
X9001248-4GMSMB0250L	110±3.0	29±0.5	LMR100	250	± 4.0	SMA MALE
X9001248-4GMSMB0XXXL	110±3.0	29±0.5	LMR100	150 ≤ 0XXX < 300	± 4.0	SMA MALE
X9001248-4GMSMB0300L	110±3.0	29±0.5	LMR100	300	± 5.0	SMA MALE
X9001248-4GMSMB0400L	110±3.0	29±0.5	LMR100	400	± 5.0	SMA MALE
X9001248-4GMSMB0XXXL	110±3.0	29±0.5	LMR100	300 ≤ 0XXX < 500	± 5.0	SMA MALE
X9001248-4GMSMB0500L	110±3.0	29±0.5	LMR100	500	± 7.0	SMA MALE
X9001248-4GMSMB0600L	110±3.0	29±0.5	LMR100	600	± 7.0	SMA MALE
X9001248-4GMSMB0XXXL	110±3.0	29±0.5	LMR100	500 ≤ 0XXX < 1000	± 7.0	SMA MALE
X9001248-4GMSMB1000L	110±3.0	29±0.5	LMR100	1000	± 1%	SMA MALE
X9001248-4GMSMB0XXXL	110±3.0	29±0.5	LMR100	1000 ≤ XXXX	± 1%	SMA MALE

*XXX : CABLE LENGTH MENTIONNED IN PART NUMBER (CUSTOMER REQUEST)




LTE Magnetic mount External antenna specifications
KYOCERA AVX produces a wide variety of standard and custom antennas to meet user needs

Mechanical Specifications (SMA MALE, RG-174)

Typical antenna dimensions in mm.

Part Number	A	Ø	Cable Type	XXXX Cable Length	Z Cable Tolerance	Connector
X9001248-4GMSMBXXXXR	110±3.0	29±0.5	RG-174	0XXX < 150	± 3.0	SMA MALE
X9001248-4GMSMB0050R	110±3.0	29±0.5	RG-174	50	± 3.0	SMA MALE
X9001248-4GMSMB0100R	110±3.0	29±0.5	RG-174	100	± 3.0	SMA MALE
X9001248-4GMSMB0150R	110±3.0	29±0.5	RG-174	150	± 4.0	SMA MALE
X9001248-4GMSMB0200R	110±3.0	29±0.5	RG-174	200	± 4.0	SMA MALE
X9001248-4GMSMB0250R	110±3.0	29±0.5	RG-174	250	± 4.0	SMA MALE
X9001248-4GMSMB0XXXXR	110±3.0	29±0.5	RG-174	150 ≤ 0XXX < 300	± 4.0	SMA MALE
X9001248-4GMSMB0300R	110±3.0	29±0.5	RG-174	300	± 5.0	SMA MALE
X9001248-4GMSMB0400R	110±3.0	29±0.5	RG-174	400	± 5.0	SMA MALE
X9001248-4GMSMB0XXXXR	110±3.0	29±0.5	RG-174	300 ≤ 0XXX < 500	± 5.0	SMA MALE
X9001248-4GMSMB0500R	110±3.0	29±0.5	RG-174	500	± 7.0	SMA MALE
X9001248-4GMSMB0600R	110±3.0	29±0.5	RG-174	600	± 7.0	SMA MALE
X9001248-4GMSMB0XXXXR	110±3.0	29±0.5	RG-174	500 ≤ 0XXX < 1000	± 7.0	SMA MALE
X9001248-4GMSMB1000R	110±3.0	29±0.5	RG-174	1000	± 1%	SMA MALE
X9001248-4GMSMB0XXXXR	110±3.0	29±0.5	RG-174	1000 ≤ XXXX	± 1%	SMA MALE

*XXX : CABLE LENGTH MENTIONNED IN PART NUMBER (CUSTOMER REQUEST)




LTE Magnetic mount External antenna specifications
KYOCERA AVX produces a wide variety of standard and custom antennas to meet user needs

Mechanical Specifications (RP-SMA MALE, LMR100)

Typical antenna dimensions in mm.

Part Number	A	Ø	Cable Type	XXXX Cable Length	Z Cable Tolerance	Connector
X9001248-4GMRMBXXXXL	110±3.0	29±0.5	LMR100	0XXX < 150	± 3.0	RP-SMA MALE
X9001248-4GMRMB0050L	110±3.0	29±0.5	LMR100	50	± 3.0	RP-SMA MALE
X9001248-4GMRMB0100L	110±3.0	29±0.5	LMR100	100	± 3.0	RP-SMA MALE
X9001248-4GMRMB0150L	110±3.0	29±0.5	LMR100	150	± 4.0	RP-SMA MALE
X9001248-4GMRMB0200L	110±3.0	29±0.5	LMR100	200	± 4.0	RP-SMA MALE
X9001248-4GMRMB0250L	110±3.0	29±0.5	LMR100	250	± 4.0	RP-SMA MALE
X9001248-4GMRMB0XXXL	110±3.0	29±0.5	LMR100	150 ≤ 0XXX < 300	± 4.0	RP-SMA MALE
X9001248-4GMRMB0300L	110±3.0	29±0.5	LMR100	300	± 5.0	RP-SMA MALE
X9001248-4GMRMB0400L	110±3.0	29±0.5	LMR100	400	± 5.0	RP-SMA MALE
X9001248-4GMRMB0XXXL	110±3.0	29±0.5	LMR100	300 ≤ 0XXX < 500	± 5.0	RP-SMA MALE
X9001248-4GMRMB0500L	110±3.0	29±0.5	LMR100	500	± 7.0	RP-SMA MALE
X9001248-4GMRMB0600L	110±3.0	29±0.5	LMR100	600	± 7.0	RP-SMA MALE
X9001248-4GMRMB0XXXL	110±3.0	29±0.5	LMR100	500 ≤ 0XXX < 1000	± 7.0	RP-SMA MALE
X9001248-4GMRMB1000L	110±3.0	29±0.5	LMR100	1000	± 1%	RP-SMA MALE
X9001248-4GMRMB0XXXL	110±3.0	29±0.5	LMR100	1000 ≤ XXXX	± 1%	RP-SMA MALE

*XXX : CABLE LENGTH MENTIONNED IN PART NUMBER (CUSTOMER REQUEST)



LTE Magnetic mount External antenna specifications
KYOCERA AVX produces a wide variety of standard and custom antennas to meet user needs

Mechanical Specifications (RP-SMA MALE, RG-174)

Typical antenna dimensions in mm.

Part Number	A	Ø	Cable Type	XXXX Cable Length	Z Cable Tolerance	Connector
X9001248-4GMRMBXXXXR	110±3.0	29±0.5	RG-174	0XXX < 150	± 3.0	RP-SMA MALE
X9001248-4GMRMB0050R	110±3.0	29±0.5	RG-174	50	± 3.0	RP-SMA MALE
X9001248-4GMRMB0100R	110±3.0	29±0.5	RG-174	100	± 3.0	RP-SMA MALE
X9001248-4GMRMB0150R	110±3.0	29±0.5	RG-174	150	± 4.0	RP-SMA MALE
X9001248-4GMRMB0200R	110±3.0	29±0.5	RG-174	200	± 4.0	RP-SMA MALE
X9001248-4GMRMB0250R	110±3.0	29±0.5	RG-174	250	± 4.0	RP-SMA MALE
X9001248-4GMRMB0XXXXR	110±3.0	29±0.5	RG-174	150 ≤ 0XXX < 300	± 4.0	RP-SMA MALE
X9001248-4GMRMB0300R	110±3.0	29±0.5	RG-174	300	± 5.0	RP-SMA MALE
X9001248-4GMRMB0400R	110±3.0	29±0.5	RG-174	400	± 5.0	RP-SMA MALE
X9001248-4GMRMB0XXXXR	110±3.0	29±0.5	RG-174	300 ≤ 0XXX < 500	± 5.0	RP-SMA MALE
X9001248-4GMRMB0500R	110±3.0	29±0.5	RG-174	500	± 7.0	RP-SMA MALE
X9001248-4GMRMB0600R	110±3.0	29±0.5	RG-174	600	± 7.0	RP-SMA MALE
X9001248-4GMRMB0XXXXR	110±3.0	29±0.5	RG-174	500 ≤ 0XXX < 1000	± 7.0	RP-SMA MALE
X9001248-4GMRMB1000R	110±3.0	29±0.5	RG-174	1000	± 1%	RP-SMA MALE
X9001248-4GMRMB0XXXXR	110±3.0	29±0.5	RG-174	1000 ≤ XXXX	± 1%	RP-SMA MALE

*XXX : CABLE LENGTH MENTIONNED IN PART NUMBER (CUSTOMER REQUEST)

