

MLG0603S36NHT000

**Applications**

Commercial Grade

**Feature**

Multilayer

**Series | Type**

MLG

**Status**

Production

**Brand**

TDK

**Size**

Length(L)	0.60mm $\pm$ 0.03mm
Width(W)	0.30mm $\pm$ 0.03mm
Thickness   Height	0.30mm $\pm$ 0.03mm
Recommended Land Pattern (A)	0.25mm Nom.
Recommended Land Pattern (B)	0.30mm Nom.
Recommended Land Pattern (C)	0.30mm Nom.

**Electrical Characteristics**

Inductance	36nH $\pm$ 3% at 100MHz
Rated Current	50mA
DC Resistance [Typ.]	1.68 $\Omega$
DC Resistance [Max.]	2 $\Omega$
Self Resonant Frequency [Min.]	1.5GHz
Self Resonant Frequency [Typ.]	1.8GHz
Q [Min.]	6 at 100MHz
Q [Typ.]	

**Other**

Operating Temp. Range	-55 to 125°C
Soldering Method	Reflow Iron Soldering
AEC-Q200	NO
Packing	Punched (Paper)Taping [180mm Reel, Tape width 8mm]
Package Quantity	15000pcs
Weight	0.0002g

! Images are for reference only and show exemplary products.





! This PDF document was created based on the data listed on the TDK Corporation website.

! All specifications are subject to change without notice.

MLG0603S36NHT000



## Characteristic Graphs (This is reference data, and does not guarantee the products characteristics.)



! Images are for reference only and show exemplary products.



! This PDF document was created based on the data listed on the TDK Corporation website.

! All specifications are subject to change without notice.

MLG0603S36NHT000



## Associated Images



! Images are for reference only and show exemplary products.  
! This PDF document was created based on the data listed on the TDK Corporation website.  
! All specifications are subject to change without notice.