

VI TELEFILTER**Filter specification****TFS 140W****1/5****Measurement condition**

Ambient temperature:	25 °C
Input power level:	0 ± 2 dBm
Terminating impedance: *	
Input:	95 Ω -21.1 pF
Output:	95 Ω -31.8 pF

Characteristics**Remark:**

The reference level for the relative attenuation a_{rel} of TFS140W is the minimum of the pass band attenuation a_{min} . This value is defined as the insertion loss a_e . The centre frequency f_C is the arithmetic mean value of the upper and lower frequencies at the 3 dB filter attenuation level relative to the insertion loss a_e . The nominal frequency f_N is fixed at **140 MHz** without tolerance. The given values are guaranteed in operating temperature range.



D a t a		typ. value		limit		
Insertion loss	$a_e = a_{min}$	8,3	dB	max.	13	dB
Nominal frequency	f_N				140,0	MHz
Centre frequency f_C	(at ambient temperature)	139,82	MHz	139,60 ...	140,40	MHz
Centre frequency f_C	(over temperature range)	.		139,05 ...	141,07	MHz
Insertion loss at f_C		8,8	dB	max.	11	dB
Amplitude ripple (peak to adjacent valley) within 133,6 MHz ... 146,4 MHz						
		0,3	dB	max.	0,9	dB
Pass bandwidth						
1	dB	15,8	MHz	min.	15	MHz
3	dB	16,9	MHz	min.	16	MHz
40	dB	20,9	MHz	max.	22	MHz
Relative attenuation						
$f_N - 40$	MHz ... $f_N - 11,9$	51	dB	min.	42	dB
$f_N + 12,5$	MHz ... $f_N + 14,5$	54	dB	min.	35	dB
$f_N + 14,5$	MHz ... $f_N + 40$	49	dB	min.	42	dB
Phase variation (within 133,6 MHz ... 146,4 MHz)						
		7	deg	max.	14	deg p-p
Triple transit signal attenuation						
		38	dB	min.	35	dB
Group delay ripple (within 133,6 MHz ... 146,4 MHz)						
		65	ns	max.	120	ns
Input power level						
		-		max.	+ 10	dBm
Operating temperature range						
		-		- 30 °C ...	+ 70	°C
Operable temperature range						
		-		- 40 °C ...	+ 85	°C
Storage temperature range						
		-		- 40 °C ...	+ 85	°C
Temperature coefficient of frequency TCf						
		-87	ppm/K		-	

*) The terminating impedances depend on parasitics and q-values of matching elements and the board used, and are to be understood as reference values only. Should there be additional questions, do not hesitate to ask for an application note or contact our design team.


Generated:**Checked / Approved:**

Tele Filter GmbH
Potsdamer Straße 18
D 14 513 TELTOW / Germany
Tel: (+49) 3328 4784-0 / Fax: (+49) 3328 4784-30
E-Mail: tft@telefilter.com

VI TELEFILTER reserves the right to make changes to the product(s) and/or information contained herein without notice. No liability is assumed as a result of their use or application. No rights under any patent accompany the sale of any such product(s) or information.

VI TELEFILTER**Filter specification****TFS 140W****2/5****Filter characteristic****Construction and pin connection**

(All dimensions in mm)



1	Ground
2	Ground
3	Ground
4	Ground
5	Output
6	Output RF Return
7	Ground
8	Ground
9	Ground
10	Ground
11	Input
12	Input RF Return


Date code: Year + week

U 2006

V 2007

W 2008

...

50 Ohm Test circuit

Tele Filter GmbH
 Potsdamer Straße 18
 D 14 513 TELTOW / Germany
 Tel: (+49) 3328 4784-0 / Fax: (+49) 3328 4784-30
 E-Mail: tft@telefilter.com

VI TELEFILTER reserves the right to make changes to the product(s) and/or information contained herein without notice. No liability is assumed as a result of their use or application. No rights under any patent accompany the sale of any such product(s) or information.

VI TELEFILTER**Filter specification****TFS 140W****3/5****Stability characteristics, reliability**

After the following tests the filter shall meet the whole specification:

1. Shock: 500g, 1 ms, half sine wave, 3 shocks each plane;
DIN IEC 68 T2 - 27
2. Vibration: 10 Hz to 500 Hz, 0,35 mm or 5 g respectively, 1 octave per min, 10 cycles per plan, 3 plans;
DIN IEC 68 T2 - 6
3. Change of temperature: -55 °C to 125°C / 30 min. each / 10 cycles
DIN IEC 68 part 2 – 14 Test N
4. Resistance to solder heat (reflow): reflow possible: twice max.;
for temperature conditions refer to the attached "Air reflow temperature conditions" on page 4;

This filter is RoHS compliant (2002/95/EG, 2005/618/EG)


Packing

Tape & Reel: IEC 286 – 3, with exception of value for N and minimum bending radius;
tape type II, embossed carrier tape with top cover tape on the upper side;


max. pieces of filters per reel: 1700
reel of empty components at start: min. 300 mm
reel of empty components at start including leader: min. 500 mm
trailer: min. 300 mm^A

Tape (all dimensions in mm)

W	: 24,00 +0,30/-0,10
Po	: 4,00 ± 0,1
Do	: 1,50 +0,1/-0
E	: 1,75 ± 0,10
F	: 11,50 ± 0,10
G(min)	: 0,60
P2	: 2,00 ± 0,1
P1	: 12,00 ± 0,1
D1(min)	: 1,50
Ao	: 7,10 ± 0,10
Bo	: 13,90 ± 0,10
Ct	: 21,5 ± 0,1

**Reel (all dimensions in mm)**

A	: 330
W1	: 24,4
W2(max)	: 30,4
N(min)	: 60
C	: 13,0




The minimum bending radius is 45 mm.

Tele Filter GmbH
Potsdamer Straße 18
D 14 513 TELTOW / Germany
Tel: (+49) 3328 4784-0 / Fax: (+49) 3328 4784-30
E-Mail: tft@telefilter.com

VI TELEFILTER reserves the right to make changes to the product(s) and/or information contained herein without notice. No liability is assumed as a result of their use or application. No rights under any patent accompany the sale of any such product(s) or information.

Air reflow temperature conditions

Conditions	Exposure
Average ramp-up rate (30°C to 217°C)	less than 3°C/second
> 100°C	between 300 and 600 seconds
> 150°C	between 240 and 500 seconds
> 217°C	between 30 and 150 seconds
Peak temperature	max. 260°C
Time within 5°C of actual peak temperature	between 10 and 30 seconds
Cool-down rate (Peak to 50°C)	less than 6°C/second
Time from 30°C to Peak temperature	no greater than 300 seconds

Chip-mount air reflow profile

Tele Filter GmbH
Potsdamer Straße 18
D 14 513 TELTOW / Germany
Tel: (+49) 3328 4784-0 / Fax: (+49) 3328 4784-30
E-Mail: tft@telefilter.com

VI TELEFILTER reserves the right to make changes to the product(s) and/or information contained herein without notice. No liability is assumed as a result of their use or application. No rights under any patent accompany the sale of any such product(s) or information.

VI TELEFILTER**Filter specification****TFS 140W****5/5****History**

Version	Reason of Changes	Name	Date
1.0	Generation of specification according to customer requirements	E. Chilla	28.03.2003
1.1	triple transit signal suppression added	Steiner	03.07.2003
1.2	generate filter specification terminating impedances added typical values added filter characteristics added test circuit added RoHS compliant added air reflow temperature conditions updated	Chilla	03.03.2006

Tele Filter GmbH
Potsdamer Straße 18
D 14 513 TELTOW / Germany
Tel: (+49) 3328 4784-0 / Fax: (+49) 3328 4784-30
E-Mail: tft@telefilter.com

VI TELEFILTER reserves the right to make changes to the product(s) and/or information contained herein without notice. No liability is assumed as a result of their use or application. No rights under any patent accompany the sale of any such product(s) or information.