




LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
CM	0		M	REVISED PER ECR-15-010337	22JUL2015	RK SC

D



C

B



RECOMMENDED LAYOUT FOR 1.57 THICK BOARD
TOLERANCES NON-ACCUMULATIVE

- PINS TO COMPLY WITH AMP SOLDERABILITY SPEC. 109-11-3.
- 0.00381 MIN MATTE TIN LEAD PLATE OVER 0.00127 MIN NICKEL.
- 0.00076 MIN GOLD PLATE IN THE LOCALIZED PLATE AREA, 0.00381 MATTE TIN LEAD IN THE LOCALIZED PLATE AREA, BOTH OVER 0.00127 MIN NICKEL.
- 0.00381 MIN MATTE TIN PLATE OVER 0.00127 MIN NICKEL.
- 0.00076 MIN GOLD PLATE IN THE LOCALIZED PLATE AREA, 0.00381 MATTE TIN IN THE LOCALIZED PLATE AREA, BOTH OVER 0.00127 MIN NICKEL.

BRASS, TIN	4	NYLON, UL94V-0	BLACK	5-770174-0
BRASS, GOLD	5	NYLON, UL94V-0	WHITE	1-770174-1
BRASS, TIN	4	NYLON, UL94V-0	WHITE	1-770174-0
BRASS, GOLD	3	NYLON, UL94V-0	WHITE	770174-2
BRASS, TIN-LEAD	2	NYLON, UL94V-0	WHITE	770174-1
MATERIAL	FINISH	MATERIAL	COLOR	PART NO.
PIN		HOUSING		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S CARPENTER 08JUN05	 TE Connectivity								
		CHK R JONES 28/JUL2003									
DIMENSIONS: mm		APVD R JONES 28JUL2003	NAME HEADER ASSEMBLY, 4 CKT, MINI UNIVERSAL MATE-N-LOK —								
		PRODUCT SPEC —									
		APPLICATION SPEC —	SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO		
MATERIAL —		FINISH —	WEIGHT —	A2 00779		C-770174		—			
CUSTOMER DRAWING			SCALE		5:1		SHEET		1 OF 1	REV	M