

Product data sheet

Specifications



3ft (0.9144m) Stainless Flex Pipe Kit 1" MPT to 1" FPT Union

ACAC10011

General

Maximum Recommended Flow Rate	22 gal(US)/min (1.4 l/s)
Piping Material	Stainless steel
Pressure sensor size	300 psi (2068.4 kPa)
Fluid connection type	NPT female NPT male
Minimum Fluid Temperature	42 °F (6 °C)
Maximum Fluid Temperature	55 °F (13 °C)
Pressure Drop per foot (0.305m)	0.92 ft of water/ft @ 19.97 gal(US)/min (1.26 l/s)

Physical

Length	3 ft (0.9 m)
Tube diameter	1 in (25.4 mm)
Product Weight	3.00 lb(US) (1.36 kg)

Ordering and shipping details

GTIN	731304249221
------	--------------

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	5.0 in (12.7 cm)
Package 1 Width	29.02 in (73.7 cm)
Package 1 Length	29.02 in (73.7 cm)
Package weight(Lbs)	11.53 lb(US) (5.23 kg)

Contractual warranty

Warranty (in months)	12
----------------------	----

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Longer

Lifetime extension	
Repair	No

Use Again

Repack and remanufacture	
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Image of product / Alternate images

Alternative

