




**Part Number :** [551000670](#)

**Product Description :** 2.00mm Pitch Serial I/O Connector, Plug Kit, Wire-to-Wire, Solder Type, 6 Circuits, Bag

**Series Number :** 55100

**Status :** Active

**Product Category :** I/O Connectors



---

## Documents and Resources

### Drawings

[551000670 sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

### Specifications


[551000680AS-A00.pdf](#)

[PS-54280-005-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Compliant with Exemption 33; 44; 34
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains 2-(2H-Benzotriazol-2-yl)-4-(1,1,3,3-tetramethylbutyl)phenol; Perfluorobutane sulfonic acid (PFBS) and its salts per D(2025)7771-DC (04 Feb 2026)

	SCIP:1f489e60-cb6f-4d18-9570-74fc16b4d6ff
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

### Additional Product Compliance Information

## Part Details

### General

Status	Active
Category	I/O Connectors
Series	55100
Description	2.00mm Pitch Serial I/O Connector, Plug Kit, Wire-to-Wire, Solder Type, 6 Circuits, Bag
Application	Wire-to-Wire
Component Type	Plug
Product Name	2.00mm I/O Connectors
Type	N/A
UPC	822348181865

### Electrical

Current - Maximum per Contact	2.0A
Shielded	Yes
Voltage - Maximum	125V AC (RMS)/DC

## Physical

Circuits (Loaded)	6
Circuits (maximum)	6
Color - Resin	Black, Gray
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze, Stainless Steel
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic, Polycarbonate
Net Weight	9414.493/mg
Orientation	Vertical
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Plating min - Mating	0.762µm
Plating min - Termination	2.032µm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +85°C
Termination Interface Style	N/A
Wire Insulation Diameter	2.10mm max.
Wire Size (AWG)	16, 18, 20, 22, 24, 26, 28

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
2.00mm Pitch IEEE 1394-1995 Shielded I/O PCB Socket, Right-Angle, Flat, Surface Mount, 6 Circuits, Tray Packaging	<a href="#"><u>534620629</u></a>
2.00mm Pitch Serial I/O Connector, Socket Kit, Wire-to-Wire Crimp Type, Without Flange, 6 Circuits	<a href="#"><u>5006550609</u></a>
2.00mm Pitch Serial I/O Connector, Socket Kit, Wire-to-	<a href="#"><u>5006550619</u></a>

Wire Crimp Type, With Flange, 6 Circuits	
2.00mm Pitch Serial I/O Connector, Receptacle Kit, Wire-to-Wire, Solder Type, 6 Circuits	<u>542800609</u>

---

This document was generated on Apr 29, 2026