
Part Number : 2076025088
Product Description : Grounding Jumper with Insulation, Right Angle to Right Angle, 48x14/30 Braid Type, 305.00mm Length
Series Number : 207602
Status : Active
Product Category : Busbars



Documents and Resources

Drawings

2076025088_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

2076025000-PS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

Downloaded from Arrow.com.

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Busbars
Series	207602
Description	Grounding Jumper with Insulation, Right Angle to Right Angle, 48x14/30 Braid Type, 305.00mm Length
Keyword	grounding jumpers, grounding strap, grounding straps, ground strap, ground straps, busbar
Product Name	Grounding Jumper
UPC	195842918528

Electrical

Current - Maximum per Contact	150.0A

Physical

Approximate AWG Equivalent	2
Approximate Circular Mils	67200
Braid Type	48x14/30
Insulation	Heat Shrink Sleeve
Length	305.00mm
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	201.000/g

Downloaded from Arrow.com.

Orientation	Right-Angle-to-Right-Angle
Packaging Type	Carton

Downloaded from Arrow.com.