Part Number : 936000018
Product Description : Heavy-Duty Metal Cable Gland - 5 Bar, for 11.00-18.00mm Cable, Pg21 Thread
Series Number : 93600
Status : Active
Product Category : Heavy-Duty Cable Glands
Engineering Part Number : 7000.6828.0



Documents and Resources

Drawings

936000018_sd.pdf

STEP AP242

SOLIDWORKS

Creo

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)7771-DC (04 Feb 2026) SCIP:90fdec01-f090-4e58-8d9e-e93cc1743ee4
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

Downloaded from Arrow.com.

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Cable Glands
Series	93600
Description	Heavy-Duty Metal Cable Gland - 5 Bar, for 11.00-18.00mm Cable, Pg21 Thread
Cable Gland Type	IP68 - 5 Bar
IP Rating	IP68
Product Name	Heavy-Duty Connectors
UPC	887191821009

Physical

Cable Diameter	11.00-18.00mm
Material - Cable Gland	Brass
Material - Plating	Nickel
Net Weight	67.000/g
Packaging Type	Bag
Panel Cutout Diameter	28.60mm
Temperature Range - Operating	-40° to +125°C
Thread Size	Pg21
Thread Type	(Pg)
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP68

Downloaded from Arrow.com.

Mates With / Use With

Use with Part(s)

Description	Part Number
Use With	Industrial connector hoods and housings

Downloaded from Arrow.com.