



Pushing Performance
Since 1945

Ha-VIS eCon 3070GB-A



Image is for illustration purposes only. Please refer to product description.

Part number	24 03 407 0010
Specification	Ha-VIS eCon 3070GB-A
HARTING eCatalogue	https://b2b.harting.com/24034070010

Identification

Series	Ha-VIS eCon 3000
Element	Industrial Ethernet Switches
Specification	Unmanaged
Type of Ethernet	Full Gigabit Ethernet

Version

Total number of ports	7
Fixing	35 mm DIN rail acc. to EN 60715
Switching technology	Store and Forward
Frame size	10 kB
MAC table size	8k Entries
Packet buffer size	1 Megabit
Non blocking	Yes
Quality of service	Yes
Energie Efficient Ethernet	Yes
Flow control	Off
Signal contact	No
Pack contents	Pluggable screw contact for power supply Assembly instructions

Termination data

Nominal voltage	24 V DC 48 V DC
Permissible voltage	18 ... 60 V DC



Pushing Performance
Since 1945

Termination data

Surge protection	Yes
Operating current	<182 mA @ 24 V DC <93 mA @ 48 V DC
Supply circuit	SELV (Circuit Breaker 10 A)
Starting current	<1.6 A @ 24 V DC <3.2 A @ 48 V DC
Overcurrent protection	12 A At input
Power consumption	<4.37 W @ 24 V DC
Termination method	Pluggable screw contact
Number of contacts	3
Conductor cross-section	0.08 ... 2.5 mm ²
Conductor cross-section	AWG 28 ... AWG 12
Pinout	+ / - / FE
Reverse polarity proof	Yes

Technical characteristics

Operating temperature	0 ... +55 °C
Storage temperature	-40 ... +85 °C
Relative humidity	0 ... 95 % Non-condensing (operation) 0 ... 95 % Non-condensing (storage/transport)
Air pressure	≥795 hPa
Degree of protection acc. to IEC 60529	IP30 mated condition
MTBF	≈850,000 h

Ethernet ports copper

10/100/1000 Mbit/s (RJ45-Ports)	7 x
Gigabit-Ethernet Ports 10/100/1000 Mbit/s (RJ45-Ports)	
Transmission standard: 10BASE-T, 100BASE-TX, 1000BASE-T	
Transmission physics: Twisted Pair Cat. 5	7 x
Transmission length: 100 m	
Data rate: 10/100/1000 Mbit/s	
Auto-negotiation: yes	
Auto-polarity: yes	
Auto-MDI(X): yes	
Transmission standard	10BASE-Te 100BASE-TX EEE 1000BASE-T EEE
Auto-negotiation	Yes



Pushing Performance
Since 1945

Ethernet ports copper

Auto-polarity	Yes
Auto-MDI(X)	Yes
Transmission physics	Twisted Pair Cat. 5
Data rate	10 Mbit/s
	100 Mbit/s
	1,000 Mbit/s
Transmission length	100 m

Material properties

Material (hood/housing)	Aluminium (anodised) Steel sheet (powder-coated)
Length	107.5 mm
Width	25 mm
Height	142 mm
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel

Specifications and approvals

Specifications	EN 55022 Radio disturbance characteristics EN 61000-4-2 Electrostatic discharge (ESD) EN 61000-4-3 Electromagnetic field EN 61000-4-4 Rapid transients (burst) EN 61000-4-5 Surge voltages EN 61000-4-6 conducted disturbances EN 61000-6-4 emission standard IEC 60068-2-6 Vibration (sinusoidal) IEEE 802.3
UL / CSA	UL 508 NRAQ.E253944 CSA-C22.2 No. 142 NRAQ7.E253944
CE	Yes
Approvals	DNV GL
PROFINET	Yes



Pushing Performance
Since 1945

Specifications and approvals

EtherNet/IP	Yes
FCC	Yes

Commercial data

Packaging size	1
Net weight	490 g
Country of origin	Germany
European customs tariff number	85176200
GTIN	5713140148741
eCl@ss	19170130 Network switch (general application)