

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact carrier, Universal, 5-position, Socket, straight, M8, coding: B, PCB mounting, SMD reflow, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1238976

Your advantages

- Reduced mounting costs thanks to two-piece device connector
- Packaging available for automated pick and place assembly
- All common pin assignments and codings available
- Easy device integration thanks to mechanical port screw connections with threaded attachment, press-in contour or direct integration in the front plate

Commercial data

Item number	1412222
Packing unit	60 pc
Minimum order quantity	60 pc
Sales key	AB22
Product key	ABQHCS
GTIN	4046356988315
Weight per piece (including packing)	2.94 g
Weight per piece (excluding packing)	2.16 g
Customs tariff number	85366990
Country of origin	DE

# SACC-CI-M8FSB-5P SMD T - Contact carrier



1412222

<https://www.phoenixcontact.com/us/products/1412222>

## Technical data

### Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
--------------------	--

### Product properties

Product type	Contact insert
Application	Data/signal
Sensor type	Universal
Number of positions	5
Seal present	no
Shielded	no
Coding	B
Thread type	M8

### Insulation characteristics

Overvoltage category	III
----------------------	-----

### Electrical properties

Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\leq 100 \text{ M}\Omega$
Nominal voltage $U_N$	30 V AC 30 V DC
Nominal current $I_N$	3 A

### Connection data

Connection method	SMD reflow
-------------------	------------

### Interfaces

Bus system	DeviceNet™
Signal type/category	Universal

### Material specifications

Flammability rating according to UL 94	V0
Contact material	CuZn
Contact surface material	Au
Contact carrier material	PA

### Connector

Connection 1
--------------

# SACC-CI-M8FSB-5P SMD T - Contact carrier



1412222

<https://www.phoenixcontact.com/us/products/1412222>

Head design	Socket
Head cable outlet	straight
Head thread type	M8
Coding	B

## Cable/line

Signal type/category	Universal
----------------------	-----------

## Mechanical properties

### Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection (when plugged in)	IP67 (correctly plugged in and locked)
Degree of protection	IP67 (correctly plugged in and locked) IP67, when plugged in
Ambient temperature (operation)	-25 °C ... 105 °C (Plug / socket) -55 °C ... 105 °C (without mechanical actuation)

## Standards and regulations

Standard designation	M8 circular connector
Standards/specifications	according to IEC 61076-2-104

## Mounting

Mounting type	PCB mounting
---------------	--------------

## Packaging specifications

Type of packaging	Tray
-------------------	------

# SACC-CI-M8FSB-5P SMD T - Contact carrier


1412222

<https://www.phoenixcontact.com/us/products/1412222>



## Drawings

Schematic diagram



Pin assignment of M8 socket, 5-pos., B-coded

# SACC-CI-M8FSB-5P SMD T - Contact carrier




1412222

<https://www.phoenixcontact.com/us/products/1412222>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1412222>

	<b>cULus Recognized</b> Approval ID: E221474-20160506			
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
	30 V	3 A	-	-

# SACC-CI-M8FSB-5P SMD T - Contact carrier



1412222

<https://www.phoenixcontact.com/us/products/1412222>

## Classifications

### ECLASS

ECLASS-13.0	27440110
-------------	----------

### ETIM

ETIM 9.0	EC003568
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# SACC-CI-M8FSB-5P SMD T - Contact carrier



1412222

<https://www.phoenixcontact.com/us/products/1412222>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	7ee4087b-74e5-4efd-9eda-27f1980f66ff

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)