


COAXIAL CONNECTOR, SMB, 50 Ohm, Straight bulkhead cable jack (female)
24_SMB-50-1-10/111_N

Properties

- Snap-on mechanism provides a fast and reliable connection
- Ideal for applications with high packaging density
- Applicable in frequencies up to 4 GHz



Product configuration		
Interface type	Gender	Standard
SMB	jack	IEC 60169-10_MIL-STD-348A/311_CECC 22130

Interface and material data		
Piece parts	Material	Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer conductor	Brass	Gold Plating (Nickel underplated)
Body	Brass	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	
Fastening nut	Brass	Gold Plating (Nickel underplated)
Washer	Bronze	Gold Plating (Nickel underplated)
Crimp ferrule	Copper	Gold Plating (without Nickel underplating)

Electrical data	
Impedance	50 Ω
Interface frequency	4 GHz

Mechanical data	
Weight	0.0018 kg
Mating cycles	500
Cable entry centre contact	crimped
Cable entry outer contact	crimped

Engagement / Disengagement force		
	Engagement	Disengagement
Interface force min	8 N	8 N
Interface force max	63 N	63 N

COAXIAL CONNECTOR, SMB, 50 Ohm, Straight bulkhead cable jack (female)

24_SMB-50-1-10/111_N

Environmental data	
Operation temperature	-65 °C ... 165 °C

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22543631	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead
22645690	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
22543631	24_SMB-50-1-10/111_NE	Single
22645690	24_SMB-50-1-10/111_NH	Bulk 100 pcs

Suitable cables	
Cable group	U1 - 1 mm / 50 Ohm
Suitable cables	RG_196_A/U
	RG_178_B/U
	ENVIROFLEX_178

Additional Information	
Only as assembly	No

Suitable tools		
Item number	Item description	Type of tool
22543181	76_Z-0-2-1	Crimping dies

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2558 / Date of publication: 11.07.2025 / uncontrolled copy