

preLink RJ45 Keystone module angled




Image is for illustration purposes only. Please refer to product description.

Part number	20 82 500 0002
Specification	preLink RJ45 Keystone module angled
HARTING eCatalogue	https://b2b.harting.com/20825000002

Identification

Category	Connectors
Series	preLink®
Element	Female module
Specification	With terminal block

Version

Termination method	preLink® IDC insulation displacement termination
Size	Keystone version
Pack contents	24 pieces

Technical characteristics

Limiting temperature	-40 ... +85 °C
Degree of protection acc. to IEC 60529	IP20
Transmission characteristics	Cat. 6A Class E _A up to 500 MHz
Vibration resistance	5.72 m/s ² acc. to IEC 61373 Category 1 Class B
Shock resistance	5 g / 30 ms, 5 shocks / axis and direction acc. to IEC 61373 Category 1 Class B

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No

Page 1 / 2 | Creation date 2020-05-17 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application.

HARTING Electronics GmbH | Marienwerderstraße 3 | 32339 Espelkamp | Germany
Phone +49 5772 47-97200 | electronics@HARTING.com | www.HARTING.com



Pushing Performance

Material properties

REACH SVHC substances	No
-----------------------	----

Specifications and approvals

Approvals	DNV GL
PROFINET	Yes

Commercial data

Packaging size	24
Net weight	23.71 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440205 Contact insert for industrial connectors