

Top View LEDs 67-21U-UYD8395V1AB1828Z2-2T0C-AM



Features

Lead (Pb) Free Product - RoHS Compliant

- P-LCC-2 package.
- Colored Clear resin.
- Wide viewing angle 120°.
- Inner reflector and white package.
- Qualification according to AEC-Q101 rev C.
- Precondition: Bases on JEDEC J-STD 020D Level 3.
- Automotive reflow profile (IR reflow or wave soldering)
- Compliance with EU REACH.

Applications

- Automotive Lighting Interior and Exterior.
- Signal and Symbol Luminary.
- Commercial and Industrial Illumination.
- Backlight: LCD, Switches, Push buttons.

Device Selection Guide

Chip Materials	Emitted Color	Resin Color
AlGaInP	Brilliant Yellow	Water Clear

Absolute Maximum Ratings (Ta=25 °C)

Parameter	Symbol	Rating	Unit
Reverse Voltage	VR	10	V
Forward Current	I _F	70	mA
Peak Forward Current (Duty 1/10 @1KHz)	I _{FP}	100	mA
Power Dissipation	P _d	196	mW
Junction Temperature	T _j	125	
Operating Temperature	T _{opr}	-40 ~ +100	
Storage Temperature	T _{stg}	-40 ~ +110	
Thermal Resistance	R _{th J-A}	250	K/W
	R _{th J-S}	150	K/W
ESD (Classification acc. AEC Q101)	ESD _{HBM}	2000	V
	ESD _{MM}	200	V
Soldering Temperature	T _{sol}	Reflow Soldering : 260 Hand Soldering : 350	for 30 sec. for 3 sec.

Electro-Optical Characteristics (Ta=25 °C)

Parameter	Symbol	Min.	Typ.	Max.	Unit	Condition
Luminous Intensity	I _v	710	---	1800	mcd	
Viewing Angle	2θ _{1/2}	---	120	---	deg	
Dominant Wavelength	λ _d	583	---	595	nm	I _F = 20mA
Forward Voltage	V _F	1.80	---	2.80	V	
Reverse Current	I _R	---	---	10	μA	VR=10V

Note:

1. Tolerance of Luminous Intensity: ±11%
2. Tolerance of Dominant Wavelength : ±1nm
3. Tolerance of Forward Voltage: ±0.1V

Bin Range of Luminous Intensity

Bin Code	Min.	Max.	Unit	Condition
V1	710	900		
V2	900	1120		
AA	1120	1400	mcd	
AB	1400	1800		


Bin Range of Dominant Wavelength

Bin Code	Min.	Max.	Unit	Condition
A5	583	586		
A6	586	589		
A7	589	592	nm	
A8	592	595		

Bin Range of Forward Voltage


Bin Code	Min.	Max.	Unit	Condition
G3-1	1.80	2.00		
G3-2	2.00	2.20		
G3-3	2.20	2.40		
G3-4	2.40	2.60	V	
G3-5	2.60	2.80		I _F = 20mA



Typical Electro-Optical Characteristics Curves(Ta=25 °C)
Typical Curve of Spectral Distribution







Note: $V(\lambda)$ =Standard eye response curve;

Diagram Characteristics of Radiation






Package Dimension



Recommended solder pad




Note: Tolerances unless mentioned ± 0.1 mm. Unit = mm

Moisture Resistant Packing Materials Label Explanation

- CPN: Customer's Product Number
- P/N: Product Number
- QTY: Packing Quantity
- CAT: Luminous Intensity Rank
- HUE: Chromaticity Coordinates Rank
- REF: Forward Voltage Rank
- LOT No: Lot Number




Reel Dimensions



Note: Tolerances unless mentioned ± 0.1 mm. Unit = mm


Carrier Tape Dimensions: Loaded Quantity 2000 pcs Per Reel



Note:

1. Tolerances unless mentioned ±0.1mm. Unit = mm
2. Minimum packing amount is 2000 pcs per reel

Moisture Resistant Packing Process




Note: Tolerances unless mentioned ±0.1mm. Unit = mm


Precautions for Use

1. Soldering Condition (Reference: IPC/JEDEC J-STD-020D)


a. IR reflow



b. Wave soldering reflow



(B) Recommend soldering pad



Note: Tolerances unless mentioned ± 0.1 mm. Unit = mm

2. Current limiting

A resistor should be used to limit current spikes that can be caused by voltage fluctuations. Otherwise damage could occur.

3. Storage

- 3.1 Moisture proof bag should only be opened immediately prior to usage.
- 3.2 Environment should be less than 30°C and 60% RH when moisture proof bag is opened.
- 3.3 After opening the package MSL Conditions stated on page 1 of this spec should not be exceeded.
- 3.4 If the moisture sensitivity card indicates higher than acceptable moisture, the component should be baked at min. 60deg +/-5deg for 24 hours.

4. Iron Soldering

Hand soldering is not recommended for regular production. These guidelines are for rework only. Soldering iron tip should contact each terminal no more than 3 sec at 350°C, using soldering iron with nominal power less than 25W. Allow min. 2 sec. between soldering intervals.

5. Usage

Do not exceed the values given in this specification.

Application Restrictions

High reliability applications such as military/aerospace, automotive safety/security systems, and medical equipment may require different product. If you have any concerns, please contact Everlight before using this product in your application. This specification guarantees the quality and performance of the product as an individual component. Do not use this product beyond the specification described in this document.