




Color: ■ gray

Physical data		
Width		1 mm / 0.039 inches
Height		69.4 mm / 2.732 inches
Depth		33.5 mm / 1.319 inches

Mechanical data		
Mounting type		snap-on type

Material data		
Note (material data)		Information on material specifications can be found here
Color		gray
Material group		I
Insulation material (main housing)		Polyamide (PA66)
Flammability class per UL94		V0
Fire load		0.066 MJ
Weight		2.4 g

Environmental requirements					
Environmental Testing			Environmental Testing		
Test specification:	DIN EN 50155 (VDE 0115-200):2022-06		Test duration per axis		10 min.
Railway applications – Rolling stock – Electronic equipment			Test directions		X, Y and Z axes
Test procedure:	DIN EN 61373 (VDE 0115-0106):2011-04		Monitoring of contact faults and interrup- tions		Passed
Railway applications – Rolling stock equipment – Vibration and shock tests			Voltage drop measurement before and after each axis		Passed
Spectrum/Mounting location	Service life test, Category 1, Class A/B		Simulated service life test through in- creased levels of noise-like oscillations		Test passed according to Section 9 of the standard
Functional test with noise-like oscillations	Test passed according to Section 8 of the standard		Frequency		f ₁ = 5 Hz to f ₂ = 150 Hz
Frequency	f ₁ = 5 Hz to f ₂ = 150 Hz		Acceleration		0.572g (highest test level used for all axes)
Acceleration	0.101g (highest test level used for all axes)		Test duration per axis		5 h

Environmental Testing

Test directions	X, Y and Z axes
Extended testing: Monitoring of contact faults and interruptions	Passed
Extended testing: Voltage drop measurement before and after each axis	Passed
Shock test	Test passed according to Section 10 of the standard
Shock pulse form	Half sine
Acceleration	5g (highest test level used for all axes)
Shock duration	30 ms
Number of shocks (per axis)	3 pos. und 3 neg.
Test directions	X, Y and Z axes
Extended testing: Monitoring of contact faults and interruptions	Passed
Extended testing: Voltage drop measurement before and after each axis	Passed
Vibration and shock stress for rolling stock equipment	Passed

Commercial data

Product Group	22 (TOPJOB S)
PU (SPU)	100 (25) pcs
Packaging type	Box
Country of origin	CN
GTIN	4044918121835
Customs tariff number	85389099990

Product Classification

UNSPSC	39121702
eCl@ss 10.0	27-14-11-33
eCl@ss 9.0	27-14-11-33
ETIM 9.0	EC000886
ETIM 10.0	EC000886
ECCN	NO US CLASSIFICATION

Environmental Product Compliance

RoHS Compliance Status	Compliant, No Exemption
------------------------	-------------------------

Approvals / Certificates

Declarations of conformity and manufacturer's declarations



Approval	Standard	Certificate Name
Railway WAGO GmbH & Co. KG	-	Railway Ready



Downloads			
Environmental Product Compliance			
Compliance Search			
Environmental Product Compliance 2016-1291			↓

Documentation			
Bid Text			
2016-1291	19.02.2019	xml 2.51 KB	↓
2016-1291	28.04.2017	doc 23.50 KB	↓

CAD/CAE-Data	
CAD data	CAE data
2D/3D Models 2016-1291	EPLAN Data Portal 2016-1291
↓	↓
	WSCAD Universe 2016-1291
	↓
	ZUKEN Portal 2016-1291
	↓