










THIS DRAWING IS A CONTROLLED DOCUMENT. FILE NO. 1583006

TOOL NUMBER 	WIRE SIZE mm ² [AWG] 	INSULATION DIAMETER mm [in.] 	INSULATION ADJUST 	STRIP LENGTH mm [in.] 	FLIP LOCATOR 	CRIMP HEIGHT mm [in.] 	CONTACT PART NUMBERS [△]		CONTACT DESCRIPTION	APPLICATION SPECIFICATION
							LOOSE PIECE 	STRIP FORM 		
91558-1 91558-3	0.50 [20] 0.85 [18]	1.80-2.80 [071-.110]	NO	3.8-4.8 [150-.189]	NO	1.05-1.22 [041-.048] 1.05-1.32 [041-.052] 1.35-1.52 [053-.060]	175218-[] 175289-[]	175196-[] 175286-[]	DYNAMIC Series D-3(L) Contacts	114-5148
91559-1 91559-3	0.20 [24] 0.30 [22] 0.50 [20]	1.20-1.60 [047-.063] 1.70-2.60 [067-.102]	NO	3.8-4.8 [150-.189]	NO	0.90-1.08 [035-.043] 0.97-1.13 [038-.044] 0.97-1.24 [038-.049]	175217-[] 175288-[]	175195-[] 175285-[]	DYNAMIC Series D-3(M) Contacts	114-5148
91560-1 91560-3	1.23-1.42 [16] 1.94-2.20 [14]	2.20-2.80 [087-.110]	NO	4.3-5.3 [169-.209]	NO	1.34-1.52 [053-.060] 1.57-1.76 [062-.069]	917511-[] 917512-[]	917484-[] 917485-[]	DYNAMIC Series D-3(2L) Contacts	114-5148
91561-1 91561-3	1.23-1.42 [16] 1.94-2.20 [14]	3.10-3.30 [122-.130] 3.50-3.80 [138-.150]	NO	4.3-5.3 [169-.209]	NO	1.34-1.52 [053-.060] 1.57-1.76 [062-.069]	353718-[] 353717-[]	353716-[] 353715-[]	DYNAMIC Series D-3(3L) Contacts	114-5148
91565-1 91565-3	0.08 [28] 0.12 [26] 0.20 [24]	0.80-1.20 [031-.047] 1.00-1.40 [039-.055]	NO	3.8-4.8 [150-.189]	NO	0.67-0.96 [026-.038] 0.67-0.98 [026-.039] 0.84-1.03 [033-.041]	175216-[] 175287-[]	175194-[] 175284-[]	DYNAMIC Series D-3(S) Contacts	114-5148
91576-1 91576-3	0.09-0.12 [28-26] 0.2 [24]	0.88-1.30 [035-.051] 1.11-1.43 [044-.056]	YES	2.9-3.9 [114-.154]	YES	0.58-0.7 [023-.028] 0.64-0.77 [025-.030]	1318108-[] 1318112-[]	1318106-[] 1318110-[]	DYNAMIC Series D-2(S) Contacts	114-5258
91595-1 91595-3	0.3-0.5 [22-20] 0.85 [18]	1.26-1.80 [050-.071] 1.79-1.90 [070-.075]	YES	2.9-3.9 [114-.154]	NO	0.87-1.03 [034-.041] 1.06-1.24 [042-.049]	1318107-[] 1318111-[]	1318105-[] 1318109-[]	DYNAMIC Series D-2(M) Contacts	114-5258
91596-1 91596-3	0.50 - 1.15 [20-18] 1.15-1.42 [16]	1.80-2.83 [071-.111] 2.35-3.23 [093-.127]	NO	4.3-4.8 [169-.189]	NO	1.35-1.50 [053-.059] 1.55-1.70 [061-.067]	1318986-6	1318985-6	DYNAMIC Series D-5(SS) Contacts	114-5206

[△] LIST OF APPLIED CONTACT PART NUMBERS MAY NOT BE COMPLETE AND IS SUBJECT TO CHANGE. FOR CURRENT INFORMATION ON TERMINAL PART NUMBERS, CONTACT THE TOOLING ASSISTANCE CENTER : 1-800-722-1111.


^③ -1 IS A CERTICRIMP II HAND TOOL ASSEMBLY.
-3 IS A CERTICRIMP II HEAD SUB-ASSEMBLY.

[△] THIS TOOL USED FOR DUAL CRIMP APPLICATION.

5. THE HAND TOOL INSTRUCTION SHEET, ALSO KNOWN AS AN "IS", FOR MOST CERTI-CRIMP II TOOLS USE IS 408-8547. IF THE TOOL HAS A FLIP LOCATOR USE IS 408-10414.

2. AMP, CERTI-CRIMP, and DYNAMIC are trademarks.

CERTI-CRIMP II DATA SHEET

DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DRAWN: M. YOUNGER 21FEB2012	MATERIAL: -	HEAT TREAT: -
0 PLC ± .05	1 PLC ± .05	2 PLC ± .05	3 PLC ± .05	CHK: B.A. WOLFE 22FEB2012	 TE Connectivity	
4 PLC ± .05	APVD: B.A. WOLFE 22FEB2012					
NAME: CERTI-CRIMP TOOL DATA SHEET DYNAMIC SERIES CONNECTORS				SCALE: -	SIZE: A1	DRAWING NO: 1583006
REVISION RECORD		DATE	OWN	APVD	SHEET 1 of 2 REV A7	

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TE AND ITS AFFILIATES. IT IS NOT TO BE DISCLOSED TO ANY OTHER PERSON OR ENTITY WITHOUT THE WRITTEN AUTHORIZATION FROM TE. © 2018 TE CONNECTIVITY

THIS DRAWING IS A CONTROLLED DOCUMENT.

TOOL NUMBER 	WIRE SIZE mm ² [AWG] 	INSULATION DIAMETER mm [in.] 	INSULATION ADJUST 	STRIP LENGTH mm [in.] 	FLIP LOCATOR 	CRIMP HEIGHT mm [in.] 	CONTACT PART NUMBERS ¹		CONTACT DESCRIPTION	APPLICATION SPECIFICATION
							LOOSE PIECE 	STRIP FORM 		
2119141-1 2119141-3	0.09-0.12 [28-26] 0.20-0.38 [24-22]	1.08-1.50 [0.042-.059]	NO	1.7-2.3 [0.67-.091]	YES	0.59-0.69 [0.23-.027] 0.69-0.79 [0.27-.031]	1827587-2 1871743-1 1903116-2 1903124-1	-	DYNAMIC Series D 1000 M TYPE CONTACTS	114-5377
2119142-1 2119142-3	0.37-0.53 [22-20] 0.87 [18]	1.40 [0.056] 2.20 [0.087]	NO	1.7-2.3 [0.67-.091]	YES	0.80-0.90 [0.031-.035] 1.10-1.20 [0.043-.047]	1827589-2 1871745-1 1903118-2 1903126-1	-	DYNAMIC Series D 1000 2L TYPE CONTACTS	114-5377
2119143-1 2119143-3	0.09-0.12 [28-26] 0.20-0.38 [24-22]	1.20-1.90 [0.047-.075]	NO	1.7-2.3 [0.67-.091]	YES	0.59-0.69 [0.23-.027] 0.69-0.79 [0.27-.031]	1827588-2 1871744-1 1903117-2 1903125-1	-	DYNAMIC Series D 1000 L TYPE CONTACTS	114-5377
2119144-1 2119144-3	0.05 [30] 0.09 [28]	0.60-1.30 [0.024-.051]	NO	1.7-2.3 [0.67-.091]	YES	0.49-0.59 [0.019-.023] 0.52-0.62 [0.020-.024]	1827586-2 1903115-2	-	DYNAMIC Series D 1000 S TYPE CONTACTS	114-5377
2119821-1 2119821-3 ⁴	DUAL WIRE APPLICATION 0.8 [18]	-	NO	2.85-3.15 [1.12-.124]	YES	1.04-1.10 [0.041-.043]	-	293389-1 293390-1	DYNAMIC Series D 1000 M TYPE CONTACTS (DUAL WIRE APPLICATION)	114-21150
2844985-1	0.50-1.15 [20-18] 1.15-1.42 [16]	1.80-2.70 [0.071-.110] 2.40-3.23 [0.094-.127]	YES	4.9-5.4 [1.92-.213]	NO	1.19-1.29 [0.047-.051] 1.35-1.45 [0.053-.057]	2040015-2 2040016-1 1-2040016-2	2040587-1 2040586-1 1-2040586-1	DYNAMIC Series D 4000 S TYPE CONTACTS	114-5369
2305681-1	0.09-0.12 [28-26] 0.20-0.38 [24-22]	1.08-1.50 [0.042-.059]	NO	1.7-2.3 [0.67-.091]	YES	0.59-0.69 [0.23-.027] 0.69-0.79 [0.27-.031]	2316671-2 2316669-2	-	HD1 M TYPE CONTACTS	114-78021
2305682-1	0.37-0.53 [22-20] 0.87 [18]	1.40 [0.056] 2.20 [0.087]	NO	1.7-2.3 [0.67-.091]	YES	0.80-0.90 [0.031-.035] 1.10-1.20 [0.043-.047]	2316671-4 2316669-4	-	HD1 2L TYPE CONTACTS	114-78021
2305683-1	0.09-0.12 [28-26] 0.20-0.38 [24-22]	1.20-1.90 [0.047-.075]	NO	1.7-2.3 [0.67-.091]	YES	0.59-0.69 [0.23-.027] 0.69-0.79 [0.27-.031]	2316671-3 2316669-3	-	HD1 L TYPE CONTACTS	114-78021
2305684-1	0.05 [30] 0.09 [28]	0.60-1.30 [0.024-.051]	NO	1.7-2.3 [0.67-.091]	YES	0.49-0.59 [0.019-.023] 0.52-0.62 [0.020-.024]	2316671-1 2316669-1	-	HD1 S TYPE CONTACTS	114-78021

¹ LIST OF APPLIED CONTACT PART NUMBERS MAY NOT BE COMPLETE AND IS SUBJECT TO CHANGE. FOR CURRENT INFORMATION ON TERMINAL PART NUMBERS, CONTACT THE TOOLING ASSISTANCE CENTER : 1-800-722-1111.

³ -1 IS A CERTICRIMP II HAND TOOL ASSEMBLY. -3 IS A CERTICRIMP II HEAD SUB-ASSEMBLY.

⁴ THIS TOOL USED FOR DUAL CRIMP APPLICATION.

5. THE HAND TOOL INSTRUCTION SHEET, ALSO KNOWN AS AN "IS", FOR MOST CERTI-CRIMP II TOOLS USE IS 408-8547. IF THE TOOL HAS A FLIP LOCATOR USE IS 408-10414.

CERTI-CRIMP II DATA SHEET

DWN: M. YOUNGER 21FEB2012		MATERIAL: -	HEAT TREAT: -
CHK: B.A. WOLFE 22FEB2012			
APVD: B.A. WOLFE 22FEB2012		STE TE Connectivity	
NAME: B.A. WOLFE			
CERTI-CRIMP TOOL DATA SHEET DYNAMIC SERIES CONNECTORS			
SCALE: -	SIZE: A1	DRAWING NO: 1583006	SHEET: 2 of 2 REV: A7

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TFCO AND AFFILIATES. IT IS NOT TO BE DISCLOSED TO ANY OTHER PERSON OR ENTITY WITHOUT THE WRITTEN AUTHORIZATION OF TFCO.