

Part Number : 1200878729
Product Description : M8 Signal, A-Coded, Double-Ended Cordset, 4 Poles, Female (90°) to Male (Straight), 0.25mm² (24 AWG), Black TPU WSOR Cable, 2.0m (6.56') Length
Series Number : 120087
Status : Active
Product Category : Industrial Cable Assemblies
Engineering Part Number : 444031B41M020

Documents and Resources

Drawings

1200878729_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant with Exemption 3 per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

Downloaded from Arrow.com.

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

Status	Active
Category	Industrial Cable Assemblies
Series	120087
Description	M8 Signal, A-Coded, Double-Ended Cordset, 4 Poles, Female (90°) to Male (Straight), 0.25mm² (24 AWG), Black TPU WSOR Cable, 2.0m (6.56') Length
IP Rating	IP67
Product Name	M8 Signal,Nano-Change (M8)
Type	Double Ended
UPC	889056074155

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	60V AC / 75V DC

Physical

Cable Diameter	4.80mm (.189")
Cable Length	2.0m (6.56')
Color - Cable Jacket	Black
Connector End A	M8 Signal
Connector End B	M8 Signal
Coupling Style	Threaded
Gender	Female-Male
Keyway	A-Coded
LED Indicator	None
Material - Cable Jacket	TPU

Downloaded from Arrow.com.

Material - Connector Body	TPU
Material - Contact	Brass
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	225.000/g
Orientation	90° to Straight
Poles	4
Temperature Range - Operating	-25° to +80°C
Wire/Cable Type	UL 21215
Wire Size (AWG)	24

Downloaded from Arrow.com.