

RTW Series

Single Output Industrial
Power Supplies

- 5 Year Warranty
- Ultra Thin Package
- SEMI F47 Compliant (high line AC)
- Universal Input (85 - 265VAC)
- High Efficiency

Key Market Segments & Applications

Semiconductor Fabrication
Test & Measurement:
LED Signs

RTW Features and Benefits

Features

- 5 Year Warranty
- Ultra Thin Package
- Wide range AC Input

Benefits

- Lower Cost of Ownership
- Allows use in small spaces
- Supports global use

Specifications

MODELS		50W	100W	150W	300W
ITEMS					
AC Input Voltage	-	85 - 265VAC (47 - 440Hz), 150-340VDC			
Input Current (100/200VAC) (Typ)	A	0.7 / 0.4	1.5 / 0.75	1.9 / 1.0	2.0 / 4.0
Inrush Current (100/200VAC)	A	14 / 28			
DC Input Voltage	V	120 - 375VDC			
Power Factor	-	Meets EN61000-3-2			
Overcurrent Protection	-	Yes, typically 105 - 125% (100 & 150W hiccup style)			
Overvoltage Protection	V	Yes, typically 120-140%. Cycle input to reset			
Hold Up Time (100/200VAC)	ms	>20			
Leakage Current (max at 240VAC)	mA	0.6	0.45	0.65	0.75
Load Regulation	%	0.4% (0-100% load change)			
Line Regulation	%	0.2% (85-132 or 170-265VAC line change)			
Remote Sense	-	Yes			
Current Share	-	No			
Remote On/Off	-	Yes, see instruction manual on website			
DC Fail Signal	-	No			
Indicator	-	Green LED = ON			
Operating Temperature	-	-10°C to +71°C, -20°C start up. See derating curves on sheet 2			
Storage Temperature	°C	-30°C to +75°C			
Humidity (non condensing)	-	10 - 95%RH			
Cooling	-	Convection			
Withstand Voltage	-	Input to Ground 2kVAC, Input to Output 3kVAC, Output to Ground 500VAC for 1 min.			
Isolation Resistance	-	>100MΩ at 25°C & 70%RH, Output to Ground 500VDC			
Vibration (non operating)	-	5 - 200Hz (10 min sweep), 19.6m/s², 1 hour (Amplitude 10mm)			
Shock (Vertical mounting) (3)	-	196m/s²			
Safety Agency Approvals (1)	-	UL60950-1, CSA60950-1 (cUL), EN60950-1, CE Mark			
Line Dip	-	Complies with SEMI F47 (200VAC line only)			
Conducted & Radiated EMI	-	EN55011 / EN55022-B, FCC-B			
Immunity	-	IEC61000-4-2 (Level 4), -3, -4 (Level 3), -5 (Level 4)			
Weight (Typ)	g	290	450	600	1300
Size (WxHxD)	mm	22 x 82 x 124	25 x 82 x 160	30 x 92 x 180	40 x 120 x 250
Warranty	yrs	5			

Notes: (1) Consult Sales Office for use under DC Input conditions (2) 100/200VAC (3) Non operating, 11 ±5ms, 3 directions, 3 times each.

Model Selector


Model	Voltage (V)	Adjustment Range	Max Current (A)	Max Power (W)	Ripple/Noise (mV)	Efficiency (typ)% ²	Pack Size
RTW03-12R	3.3V	2.6 - 4.0	12.5	41.2	120	75 / 77	50W
RTW03-25R	3.3V	2.6 - 4.0	25	82.5	120	79 / 81	100W
RTW03-35R	3.3V	2.6 - 4.0	35	115.5	120	80 / 83	150W
RTW03-70RH	3.3V	1.8 - 3.6	70	231	120	83 / 86	300W
RTW05-10R	5V	4.0 - 5.8	10	50	120	80 / 82	50W
RTW05-20R	5V	4.0 - 5.8	20	100	120	83 / 85	100W
RTW05-30R	5V	4.0 - 5.8	30	150	120	83 / 86	150W
RTW05-60RH	5V	3.5 - 5.6	60	300	120	84 / 87	300W
RTW12-4R3	12V	9.6 - 13.2	4.3	51.6	150	81 / 83	50W
RTW12-8R4	12V	9.6 - 13.2	8.4	100.8	150	84 / 86	100W
RTW12-12R	12V	9.6 - 13.2	12.5	150	150	84 / 87	150W
RTW12-25RH	12V	7.2 - 14.4	25	300	150	83 / 86	300W
RTW15-3R5	15V	12.0 - 16.5	3.5	52.5	150	82 / 85	50W
RTW15-6R7	15V	12.0 - 16.5	6.7	100.5	150	85 / 87	100W
RTW15-10R	15V	12.0 - 16.5	10	150	150	84 / 87	150W
RTW15-20RH	15V	10.5 - 18.0	20	300	150	83 / 86	300W
RTW24-2R2	24V	19.2 - 26.4	2.2	52.8	200	82 / 85	50W
RTW24-4R2	24V	19.2 - 26.4	4.2	100.8	200	85 / 87	100W
RTW24-6R3	24V	19.2 - 26.4	6.3	151.2	150	86 / 88	150W
RTW24-13RH	24V	16.8 - 26.4	13	312	200	85 / 88	300W
RTW28-1R8	28V	22.4 - 30.8	1.8	50.4	200	82 / 85	50W
RTW28-3R6	28V	22.4 - 30.8	3.6	100.8	200	85 / 87	100W
RTW28-5R4	28V	22.4 - 30.8	5.4	151.2	200	86 / 88	150W
RTW28-11RH	28V	19.6 - 33.6	11	308	200	85 / 88	300W
RTW48-1R1	48V	38.4 - 52.8	1.1	52.8	300	82 / 85	50W
RTW48-2R1	48V	38.4 - 52.8	2.1	100.8	300	85 / 88	100W
RTW48-3R2	48V	38.4 - 52.8	3.2	153.6	200	86 / 89	150W
RTW48-6R5H	48V	33.6 - 55.0	6.5	312	300	86 / 89	300W

Notes: (2) 100/200VAC See website technical downloads for detailed information


Options

Suffix	Description
L	Vertical Terminal Block (option for 50W & 100W models only)
C	Cover (50W, 100W & 150W models)
H	Cover (300W models)

Derating Curves RTW50-150W Series



Derating Curve RTW 300W Series





TDK-Lambda France SAS

ZAC des Delaches
CS 41077
9 rue Thuillere
91978 Villebon Courtaboeuf
France
Tel: +33 1 60 12 71 65
Fax: +33 1 60 12 71 66
france@fr.tdk-lambda.com
www.fr.tdk-lambda.com



Italy Sales Office

Via dei Lavoratori 128/130
20092 Cinisello Balsamo (MI)
Italy
Tel: +39 02 61 29 38 63
Fax: +39 02 61 29 09 00
info.italia@it.tdk-lambda.com
www.it.tdk-lambda.com



Netherlands

info@tdk-lambda.nl
www.tdk-lambda.nl



TDK-Lambda Germany GmbH

Karl-Bold-Strasse 40
77855 Achern
Germany
Tel: +49 7841 666 0
Fax: +49 7841 5000
info.germany@de.tdk-lambda.com
www.de.tdk-lambda.com



Austria Sales Office

Aredstrasse 22
2544 Leobersdorf
Austria
Tel: +43 2256 655 84
Fax: +43 2256 645 12
info.germany@de.tdk-lambda.com
www.de.tdk-lambda.com



Scandinavia Sales Office

Valdemarsgade 7
4100 Ringsted
Denmark
Tel: +45 24 63 95 65
Fax: +45 69 80 44 99
info@de.tdk-lambda.com
www.emea.tdk-lambda.com



Switzerland Sales Office

Bahnhofstrasse 50
8305 Dietlikon
Switzerland
Tel: +41 44 850 53 53
Fax: +41 44 850 53 50
info@de.tdk-lambda.com
www.de.tdk-lambda.com



TDK-Lambda UK Ltd.

Kingsley Avenue
Ilfracombe
Devon EX34 8ES
United Kingdom
Tel: +44 (0) 12 71 85 66 66
Fax: +44 (0) 12 71 86 48 94
powersolutions@uk.tdk-lambda.com
www.uk.tdk-lambda.com



TDK-Lambda Ltd.

Kibbutz
Givat Hashlosa 48800
Israel
Tel: +9 723 902 4333
Fax: +9 723 902 4777
info@tdk-lambda.co.il
www.tdk-lambda.co.il



C.I.S.

Commercial Support:

Tel: +7 (495) 665 2627

Technical Support:

Tel: +7 (812) 658 0463
info@tdk-lambda.ru
www.tdk-lambda.ru

Local Distribution

www.emea.tdk-lambda.com