

6

5

4

3

2

1

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/7/14	


APPROVED: _____

DATE: _____ TITLE: _____


D

POLES	DIMENSIONS INCHES [mm]	
	A	B
2	.039 [1.00]	.157 [4.00]
3	.079 [2.00]	.197 [5.00]
4	.118 [3.00]	.236 [6.00]
5	.157 [4.00]	.276 [7.00]
6	.197 [5.00]	.315 [8.00]
7	.236 [6.00]	.354 [9.00]
8	.276 [7.00]	.394 [10.00]
9	.315 [8.00]	.433 [11.00]
10	.354 [9.00]	.472 [12.00]
11	.394 [10.00]	.512 [13.00]
12	.433 [11.00]	.551 [14.00]
13	.472 [12.00]	.591 [15.00]
14	.512 [13.00]	.630 [16.00]
15	.551 [14.00]	.669 [17.00]
20	.748 [19.00]	.866 [22.00]

C



B



SPECIFICATIONS:

Material:

Insulator: Hi-Temp. Thermoplastic, rated UL 94V-0

Insulator color: Natural

Plating:

Matte Tin over Copper underplate overall

Electrical:

Operating voltage: 50 VAC max

Current rating: 1 Amp max

Contact resistance: 20 mohms max.

Insulation resistance: 100 Mohms min

Dielectric withstanding voltage: 500 VAC for 1 minute


Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant

PACKAGED ON TAPE & REEL



RECOMMENDED PC BOARD LAYOUT

ADAM TECH909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-57101.0mm WIRE TO BOARD WAFER SMT
SIDE ENTRY

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				INCHES				Holes			
.X	± .10	ØX	± .10	.XX	± .020	ØXX	± .015	.XXX	± .015	ØXXX	± .010
APPROVALS				DATE				TITLE			
DRAWN	AY			11/7/14				SIZE	PART NO.	REV.	
CHECKED	RT			11/7/14				X	1SH-A-XX-MTR-SMT-T/R	-	
APPROVED								REF:	S00723T	SCALE:	NIS
										SHEET	1 OF 1

A

A

6

5

4

3

2

1