




APPROVED: _____
DATE: _____ TITLE: _____




.100 [2.54] .025 [0.64] SQ.



Rev	AWO #	Description	Date	Appr
-		RELEASED	8/20/08	BAS
A		REDRAWN	4/21/10	
B		REVISED SPEC.	04/10/12	



RECOMMENDED PCB LAYOUT



SPECIFICATIONS:

Material: Nylon 66, rated UL 94V-0
Insulator color: White
Contacts: Brass
Plating: Tin over Copper underplate overall
Electrical:
Operating voltage: 250 VAC max
Current rating: 3 Amps max
Dielectric withstanding voltage: 1,500 VAC for 1 minute
Temperature Rating: Operating temperature: -40°C to +105°C
Environmental: Lead free, RoHS compliant

Positions: 2 thru 12
A = .100 [2.54] x No. of Positions
B = .100 [2.54] x No. of Spaces

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

RIGHT ANGLE, TIN PLATED, PCB

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES Holes .X ± .10 .XX ± .020 .XXX ± .015 APPROVALS				DATE			
DRAWN	DRY	8/20/08	SIZE	PART NO.	REV.		
CHECKED	BAS	8/20/08	X	LHS-XX-TRB	B		
APPROVED			REF: S00123T	SCALE: NTS	SHEET 1 OF 1		

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

RIGHT ANGLE, TIN PLATED, PCB

ROHS
COMPLIANT