



Copyright AFCI

Amphenol
FCI

D

1

2


3

4


5

6


DIMENSIONS



PCB LAYOUT



TERMINATION





ORDERING INFORMATION

SERIES	8609	3	48	7	1	13	7	4	8	ELF
ROWS FITTED WITH CONTACTS										
ROW a	b	c	d	e	f	g	h	i	j	k
ROW a	b	c	d	e	f	g	h	i	j	k
NO. OF CONTACTS										
TYPE OF INSULATOR										
3 ROW MALE INSULATOR										
METHOD OF MOUNTING										
STANDARD MOUNTING - STYLE C										
TERMINATION										
ANGLED SPILL										
OPTIONS										
NO OPTION										
WITH HARPOONS										
PERFORMANCE CLASS										
DIN 41612 CLASS 3										
DIN 41612 CLASS 2										
DIN 41612 CLASS 1										
AS PER MIL C 55302 / JSS 50808										
PITCH PER ROW										
5.08 mm EVEN LOADING										
LEAD FREE VERSION										

GENERAL CHARACTERISTICS & RoHS INFO

REFER DRAWING C-8609-0000A

mat'l. code SEE DWG C-8609-0000A				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family 8609							
ltr	ecn no	dr	date	tolerances unless otherwise specified				 mm scale 3:2		title DIN STANDARD HEADER DIN 41612 STYLE C							
A	I04-0084	MINI	2004-09-18	angles	linear	0.X ±0.1											
B	I05-0089	MINI	2005-05-19			0.XX ±0.1											
C	I06-0061	MINI	2006-05-31			0°±2° 0.XXX ±0.1											
D	I07-0111	KR	2007-09-05	dr	MINI K V		2004-09-18				dwg no				sheet 1 of 1		size
E	I08-0146	KR	2008-10-22	enrg	RAKHEE G		2004-09-18				C-8609-2002				A3		
F	ELX-I-41230	MJA	2021-06-16	chr	M JACOB		2021-06-16				type Product Customer Drawing						
				appd	SANOJ		2021-06-16										
sheet index		revision sheet		F	1												