


PC-102 SERIES

Dual Seal-Leak Detector or Seal-Leak & Over-Temperature Detector




Wiring Diagram

PC-102CICI-DL



PC-102CICI-LT



Ordering Information

MODEL	LINE VOLTAGE	DESCRIPTION
PC-102CICI-DL	120VAC nominal	Dual seal-leak detector uses inputs to sense seal failures and energize the output relay. Input logic direct or inverted is DIP switch selectable
PC-102CICI-LT	120VAC nominal	Seal-leak and over-temperature detector uses one input to sense seal failures and the temperature input to detect motor overheating. Configurable to suit various probes. Seal input logic direct or inverted, plus over-temperature trip reset automatic or manual, is DIP switch selectable

Description

The PC-102 is a dual-channel switch that provides dual protection against seal failures and over-temperature in submersible pumping applications.

Both units have two form-C isolated output relays and two LEDs, which illuminate when each associated output relay is energized.

The sensitivity adjustment (4.7k-100kOhms) allows you to define the input impedance at which the output relays will change state. The sensitivity for the over-temperature detector can be set to 4k Ohms with use of the DIP switches.

This unit may not be compatible with Flygt pumps.

Features & Benefits

FEATURES	BENEFITS
Finger-safe terminals	Meets IEC 61000 safety requirements
Compact design for DIN rail or surface mount	Allows flexibility in panel installation
LED Status Indicator	Visual indication of relay engagement
Two input channels	Flexibility for pump-up/pump-down or two-channel switch applications

Specifications

Input Characteristics

Frequency

50/60Hz

Functional Characteristics

Probe Sense Voltage

5vdc pulsed

Sensitivity

4.7k-100kΩ

Sensitivity (for temp)

Selectable 4kΩ with DIP switches

Input Logic

Direct or inverted

Debounce Time Delay

0.5 or 2 seconds

Output Characteristics

Relay Output Rating

(2 Form C isolated)

Pilot Duty

180VA @ 120VAC, C150

General Purpose

5A @ 240VAC

General Characteristics

Temperature Range

-20° to 55°C (-4° to 131°F)

Maximum Input Power

2 W

Depluggable Connector

Phoenix Contact-Series MSTB plugs

Output Relay

Status Indicators

LEDs

Terminal Torque

4.5 in.-lbs.

Wire range

12-20 AWG

Standards Passed

Electrostatic Discharge (ESD)

IEC 61000-4-2, Level 3, 6kV contact, 8kV air.

Radio Frequency Immunity (RFI)

IEC 61000-4-3, Level 3, 10V/m

Fast Transients

IEC 61000-4-4, Level 3, 4kV input power
2kV inputs/outputs

Safety Marks

UL

UL508 (File #E68520)

Dimensions

H 88.9 mm (3.5"); **W** 52.93 mm (2.08");
D 59.69 mm (2.35")

Weight

0.9 lb. (14.4 oz., 408.23 g)

Mounting Method

35mm DIN rail or Surface Mount
(#6 or #8 screws)