

Electronic housing - ME-IO 75,2 B 10U 7035 - 2202664

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Component housing, Lower part, Color: light gray, Width: 75.9 mm, Constructional height: 57.7 mm

RoHS

Key Commercial Data

Packing unit	1 STK
Minimum order quantity	10 STK
Weight per Piece (excluding packing)	76.000 g
Custom tariff number	85472000
Country of origin	Germany

Technical data

General

Housing type	Component housing
Housing material	Polyamide
Color	light gray

Dimensions

Length	120.6 mm
Constructional height	57.7 mm
Width	75.9 mm

Technical data

Flammability rating according to UL 94	V0
--	----

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Environmental Product Compliance

Electronic housing - ME-IO 75,2 B 10U 7035 - 2202664

Technical data

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 5.1	27371301
eCl@ss 8.0	27182702
eCl@ss 9.0	27182702

ETIM

ETIM 5.0	EC001031
----------	----------

Accessories

Accessories

Component housing upper part

Electronic housing - ME-IO 18,8 C 2U 7035 - 2201799



Component housing, Cover, Color: light gray, Width: 18.9 mm, Constructional height: 12.2 mm

Electronic housing - ME-IO 18,8 C 3U 7035 - 2201800



Component housing, Cover, Color: light gray, Width: 18.9 mm, Constructional height: 12.2 mm

Electronic housing - ME-IO 18,8 C 3U S1 7035 - 2201801



Component housing, Cover, Color: light gray, Width: 18.9 mm, Constructional height: 12.2 mm

Electronic housing - ME-IO 75,2 B 10U 7035 - 2202664

Accessories

Electronic housing - ME-IO 18,8 C 4U 7035 - 2201802



Component housing, Cover, Color: light gray, Width: 18.9 mm, Constructional height: 12.2 mm

Electronic housing - ME-IO 18,8 C 5U 7035 - 2201803



Component housing, Cover, Color: light gray, Width: 18.9 mm, Constructional height: 12.2 mm

Electronic housing - ME-IO 18,8 C 6U 7035 - 2201804



Component housing, Cover, Color: light gray, Width: 18.9 mm, Constructional height: 12.2 mm

Electronic housing - ME-IO 18,8 C 7U 7035 - 2201805



Component housing, Cover, Color: light gray, Width: 18.9 mm, Constructional height: 12.2 mm

Electronic housing - ME-IO 18,8 C 8U 7035 - 2202634



Component housing, Cover, Color: light gray, Width: 18.9 mm, Constructional height: 12.2 mm

Electronic housing - ME-IO 75,2 B 10U 7035 - 2202664

Accessories

Electronic housing - ME-IO 18,8 C 10U 7035 - 2202630



Component housing, Cover, Color: light gray, Width: 18.9 mm, Constructional height: 12.2 mm

Electronic housing - ME-IO 18,8 C 2U MC10 7035 - 2202582



Component housing, Lower part, Color: light gray, Width: 20.94 mm, Constructional height: 16.3 mm

Electronic housing - ME-IO 18,8 C 2U MC18 7035 - 2202581



Component housing, Lower part, Color: light gray, Width: 20.94 mm, Constructional height: 16.3 mm

Fiber optics

Component housing - HS LC-H-D2/ R2XC1-2,54 - 2202316



Fiber optics can be used for the ME, ME-MAX, ME-IO, ME PLC, and EH housing ranges (housing must be processed),
Color: transparent

Component housing - HS LC-H-D2/ R2XC2-2,54 - 2202317



Fiber optics can be used for the ME, ME-MAX, ME-IO, ME PLC, and EH housing ranges (housing must be processed),
Color: transparent

Electronic housing - ME-IO 75,2 B 10U 7035 - 2202664

Accessories

Component housing - HS LC-H-D2/ R2XC5-2,54 - 2202318



Fiber optics can be used for the ME, ME-MAX, ME-IO, ME PLC, and EH housing ranges (housing must be processed),
Color: transparent

Component housing - HS LC-H-D2/ R2XC10-2,54 - 2202319



Fiber optics can be used for the ME, ME-MAX, ME-IO, ME PLC, and EH housing ranges (housing must be processed),
Color: transparent

Component housing - HS LC-H-D2/ R4XC2-2,54 - 2202320



Fiber optics can be used for the ME, ME-MAX, ME-IO, ME PLC, and EH housing ranges (housing must be processed),
Color: transparent

Component housing - HS LC-H-D2/ R4XC5-2,54 - 2202321



Fiber optics can be used for the ME, ME-MAX, ME-IO, ME PLC, and EH housing ranges (housing must be processed),
Color: transparent

Component housing - HS LC-H-D2/ R4XC9-2,54 - 2202322



Fiber optics can be used for the ME, ME-MAX, ME-IO, ME PLC, and EH housing ranges (housing must be processed),
Color: transparent

Electronic housing - ME-IO 75,2 B 10U 7035 - 2202664

Accessories

Component housing - HS LC-H-D2/ R4XC10-2,54 - 2202323



Fiber optics can be used for the ME, ME-MAX, ME-IO, ME PLC, and EH housing ranges (housing must be processed),
Color: transparent

Filler plug

Electronic housing - ME-IO 18,8 F-LR 7035 - 2202635



Component housing, Filler plugs, Color: light gray, Width: 16.1 mm, Constructional height: 11.7 mm

Ground contact

Electronic housing - ME BUS FE CONTACT - 2278076



Electronics housing

Mounting material

Electronic housing - HSC-LR 9U KIT 2003 - 2201794



Component housing, Lock and Release system, Color: orange, Width: 16.2 mm

Electronic housing - ME-IO 75,2 B 10U 7035 - 2202664

Accessories

Electronic housing - HSC-LR 7U KIT 2003 - 2201795



Component housing, Lock and Release system, Color: orange, Width: 16.2 mm

Electronic housing - HSC-LR 5U KIT 2003 - 2201796



Component housing, Lock and Release system, Color: orange, Width: 16.2 mm

Electronic housing - HSC-LR 3U KIT 2003 - 2201797



Component housing, Lock and Release system, Color: orange, Width: 16.2 mm

PCB headers

Printed-circuit board connector - HSCH 2,5-3U/12 9005 - 2201788



Header, Nominal current: 8 A, Rated voltage (III/2): 300 V, Number of positions: 12, Pitch: 5 mm, Connection method: Plug / solder connection, Color: black, Contact surface: Tin, Mounting: Soldering, Please observe the derating curve of the item

Printed-circuit board connector - HSCH 2,5-2U/ 8 9005 - 2201789



Header, Nominal current: 8 A, Rated voltage (III/2): 300 V, Number of positions: 8, Pitch: 5 mm, Connection method: Plug / solder connection, Color: black, Contact surface: Tin, Mounting: Soldering, Please observe the derating curve of the item

Electronic housing - ME-IO 75,2 B 10U 7035 - 2202664

Accessories

Printed-circuit board connector - HSCH 2,5-2U-TTTT 9005 - 2201790



Header, Nominal current: 8 A, Rated voltage (III/2): 300 V, Number of positions: 4, Pitch: 5 mm, Connection method: Plug / solder connection, Color: black, Contact surface: Tin, Mounting: Soldering, Please observe the derating curve of the item

Printed-circuit board connector - HSCH 2,5-2U-2220 9005 - 2201792



Header, Nominal current: 8 A, Rated voltage (III/2): 300 V, Number of positions: 6, Pitch: 5 mm, Connection method: Plug / solder connection, Color: black, Contact surface: Tin, Mounting: Soldering, Please observe the derating curve of the item

PCB plug

Printed-circuit board connector - HSCP-SP 2,5-1U/ 4 7035 - 2201780



Plug component, Nominal current: 8 A, Rated voltage (III/2): 300 V, Number of positions: 4, Pitch: 5 mm, Connection method: Push-in technology, Color: light gray, Contact surface: Tin, Color of the spring lever: orange

Printed-circuit board connector - HSCP-SP 2,5-1U-TT 7035 - 2201781



Plug component, Nominal current: 8 A, Number of positions: 4, Pitch: 5 mm, Connection method: Push-in technology, Color: light gray, Color of the spring lever: orange

Printed-circuit board connector - HSCP-SP 2,5-1U-20 7035 - 2201782



Plug component, Nominal current: 8 A, Rated voltage (III/2): 300 V, Number of positions: 2, Pitch: 5 mm, Connection method: Push-in technology, Color: light gray, Contact surface: Tin, Please observe the derating curve of the item

Electronic housing - ME-IO 75,2 B 10U 7035 - 2202664

Accessories

Electronic housing - ME-IO 18,8 MC 8U TRANS - 2202627



Component housing, Lower part, Color: transparent, Width: 20.94 mm, Constructional height: 16.3 mm

Electronic housing - ME-IO P 10U 7035 - 2202629



Component housing, Partition, Color: light gray, Width: 2.69 mm, Constructional height: 28 mm

Printed-circuit board connector - HSCH 1,5-3U/18 9005 - 2202232



HSC header, touch-proof, 3 units, 18 connections, please note the positioning, color: black

Printed-circuit board connector - HSCH 1,5-2U/12 9005 - 2202233



HSC header, touch-proof, 2 units, 12 connections, color: black

Electronic housing - HSCP-SP 2,5-1U/-00 7035 - 2202585



Electronic housing - ME-IO 75,2 B 10U 7035 - 2202664

Accessories

Printed-circuit board connector - HSCP-SP 2,5-1UTT-55/55-7035 - 2202607



Component housing, Color: light gray, Color of the spring lever: green

Printed-circuit board connector - HSCP-SP 2,5-1U/ 4BK 7035 - 2202569



Plug component, Number of positions: 4, Pitch: 5 mm, Connection method: Push-in technology, Color of the spring lever: black

Printed-circuit board connector - HSCP-SP 2,5-1U/ 4RD 7035 - 2202572



Plug component, Number of positions: 4, Pitch: 5 mm, Connection method: Push-in technology, Color of the spring lever: red

Printed-circuit board connector - HSCP-SP 2,5-1U/ 4BU 7035 - 2202570



Plug component, Number of positions: 4, Pitch: 5 mm, Connection method: Push-in technology, Color of the spring lever: blue

Printed-circuit board connector - HSCP-SP 2,5-1U/ 4GN 7035 - 2202571



Plug component, Number of positions: 4, Pitch: 5 mm, Connection method: Push-in technology, Color of the spring lever: green

Electronic housing - ME-IO 75,2 B 10U 7035 - 2202664

Accessories

Printed-circuit board connector - HSCP-SP 2,5-1U/ 4WH 7035 - 2202568



Plug component, Number of positions: 4, Pitch: 5 mm, Connection method: Push-in technology, Color of the spring lever: white

Printed-circuit board connector - HSCP-SP 2,5-1UTT-62/62-7035 - 2202606



Component housing, Color: light gray, Color of the spring levers: blue / red

Printed-circuit board connector - HSCP-SP 2,5-1U4-69/69-7035 - 2202605



Plug component, Number of positions: 4, Pitch: 5 mm, Connection method: Push-in technology, Color of the spring levers: blue / white

Printed-circuit board connector - HSCP-SP 2,5-1U4-99/62-7035 - 2202608



Plug component, Number of positions: 4, Pitch: 5 mm, Connection method: Push-in technology, Color of the spring levers: white / blue / white / red

Electronic housing - HSCP-SP 2,5-1U4-29/29-7035 - 2203192



Component housing, Color: light gray

Electronic housing - ME-IO 75,2 B 10U 7035 - 2202664

Accessories

Electronic housing - HSCP-SP 2,5-1U4-62/59-7035 - 2203194



Component housing, Color: light gray

Electronic housing - HSCP-SP 2,5-1U4-65/65-7035 - 2203195



Component housing, Color: light gray

Printed-circuit board connector - HSCP-SP 1,5-1U/ 6 7035 - 2202234



HSC Push-in connector, for touch-proof HSC headers, 1 unit, with integrated test point, 6-pos., color: light gray

Printed-circuit board connector - HSCP-SP 1,5-1U6-629/629-7035 - 2202609



Component housing, Color: light gray, Color of the spring levers: blue / red / white

Electronic housing - ME B-22,5 MSTBO BU 5010 - 2202235

Filler plugs, for unoccupied terminal points

Electronic housing - ME-IO 75,2 B 10U 7035 - 2202664

Accessories

Electronic housing - ME 18,8 TBUS 1,5/5-ST-3,81KMGY - 2201813



Plug component, Nominal current: 8 A, Nominal current (Ex): 8 A, Nominal voltage (Ex): 125 V, Number of positions: 5, Pitch: 3.81 mm, Color: light gray, Contact surface: Gold, Articles with gold-plated contacts, bus connectors for connecting with electronic housings

Electronic housing - ME-IO 18,8 FOOT CATCH KIT - 2201812

Component housing

Component housing - HS LC-H-D2/ R2XC4-2,54 - 2202531



Fiber optics can be used for the ME, ME-MAX, ME-IO, ME PLC, and EH housing ranges (housing must be processed), Color: transparent

Component housing - HS LC-H-D2/ R4XC4-2,54 - 2202532



Fiber optics can be used for the ME, ME-MAX, ME-IO, ME PLC, and EH housing ranges (housing must be processed), Color: transparent

Electronic housing - ME-IO 18,8 MC 8U TRANS - 2202627



Component housing, Lower part, Color: transparent, Width: 20.94 mm, Constructional height: 16.3 mm

Electronic housing - TBUS8-18,8-PPPPPPPS-7035 - 2202399

Plug component, Nominal current: 6 A, Number of positions: 8, Pitch: 2.54 mm, Color: light gray

Phoenix Contact 2016 © - all rights reserved
<http://www.phoenixcontact.com>