

Honeywell Sensing and Control

Search



3153 00300016
Thermostats
(Home : Products)

narrow your search

Products

- Controls
 - Monitoring and Lighting (352)
- Machine Safety (1705)
- Sensors (6325)
- Switches (9763)
- Wireless (4)

Technology

- Electromechanical (9306)
 - Magnetic (541)
 - Microstructure (1577)
 - Optical/Infrared (1056)
 - Thick Film (1764)
- More...

white papers

- ▶ Basic Switches Are Not Created Equal
- ▶ Applying Precision Switches
- ▶ Sensors for Medical Devices
- ▶ New Ways to Measure Torque
- ▶ Choosing Safety Switches
- ▶ Specifying Hour Meters
- ▶ SAW Torque Sensor Technology

white papers

- ▶ Basic Switches Are Not Created Equal
- ▶ Applying Precision Switches
- ▶ Sensors for Medical Devices
- ▶ New Ways to Measure Torque
- ▶ Choosing Safety Switches
- ▶ Specifying Hour Meters
- ▶ SAW Torque Sensor Technology

Need help?

[Click here to contact us](#)



Series Low Silhouette Hermetic Thermostats

Actual product appearance may vary.

[Sales & Service](#)

[Distributor Inventory](#)

[Overview](#) [Specs](#) [Documentation](#) [Application Notes](#)

Product Specifications

Functional Properties	Open on rise
Reset Type	Automatic
Amperage	2.0 A resistive
Voltage	30 Vac/Vdc
Operating Temperature	-29 °C to 177 °C [-20 °F to 350 °F]
Environmental Exposure Range	-65 °C to 260 °C [-85 °F to 500 °F]
Open Temperature	18.3 °C [65 °F]
Close Temperature	-4 °C [25 °F]
Open Tolerance	2.8 °C [5 °F]
Close Tolerance	2.8 °C [5 °F]
Dielectric Strength	MIL-STD-202, Method 301; 1250 Vac 60 Hz - Terminal to Case
Insulation Resistance	MIL-STD-202, Method 302; 500 MOhm
Contact Resistance	MIL-STD-202, Method 307; 0.050 Ohm max.
Hermetic Seal	MIL-STD-202, Method 112; Cond. C
Moisture Resistance	MIL-STD-202, Method 106
Shock	MIL-STD-202, Method 213; 100 G
Vibration	MIL-STD-202, Method 204; 20 G
Thermal Shock	MIL-STD-202, Method 107; Cond. B
Salt Spray	MIL-STD-202, Method 101; Cond. B
Housing Material	Steel housing hermetically sealed with glass-to-metal seal at terminal junction
Contact Material	Silver
Agency Approvals and Standards	Acceptance testing performed in accordance to Mil-PRF-24236, Table III
Mounting	S306 6-32 round cap stud
Series Name	3153

contacts

- ▶ Customer Service
- ▶ Technical Support
- ▶ Global Sales & Service
- ▶ View Site Demo
- ▶ Site Comments?

meet dr. larry

VIDEO - Dr. Larry Goldstein explains our newest and best technologies.



- ▶ Meet Dr. Larry

my links

- ▶ Login to iCOM
- ▶ Login as Rep/AD
- ▶ Login as Guest
- ▶ Login to Digital University

News Center

- ▶ HONEYWELL EXPANDS HAZARDOUS AREA LIMIT SWITCH FAMILY TO FEATURE A STAINLESS-STEEL SWITCH
- ▶ HONEYWELL RELEASES UNLIMITED POTENTIAL WITH NEW LIMITLESS™ WIRELESS SWITCHES
- ▶ HONEYWELL'S XYR6000 WIRELESS POSITION SENSOR ENABLES MONITORING IN HAZARDOUS AREAS AND REMOTE LOCATIONS

MICRO SWITCH Anniversary site