

6

5






4

3

2

1

used for: D-SUB COMBINATION



NOTES:

1. METAL SHELLS: STEEL; min. 320μ" TIN
2. INSULATORS: PBT GF UL 94 V-0, GREEN
3. SIGNAL CONTACTS: COPPER ALLOY
4. PLATING: min. 30μ" HARD GOLD OVER min. 50μ" NICKEL
5. CONNECTOR IS PART MARKED: PART NO: CONEC Y/W/W
6. [] = CRITICAL DIMENSION: SPC

Directive 2002/95/EC
RoHS
Compliant

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name
2001	date	name	
drawn	28.05.	Parei	
appd.	28.05.	Mickenbecker	
norm			
d-old			

tolerance



scale: 2:1 (5:1)
material: SEE NOTES

title:
D-SUB COMBINATION MALE
24W7P SOLDER CUP

dwg no: AutoCAD 2000 DIN-A
13K1A262A 3
sh: 1/1

part no: 3024W7PCM99A10X

CONEC