

CONNECTOR BODY: PHOSPHOR BRONZE, AU 0.05 um MIN. PLATED OVER NI 1.0 um MIN.
CONNECTOR CENTER CONTACT: PHOSPHOR BRONZE , AU 0.1 um MIN. PLATED OVER NI 1.0 um MIN.
CONNECTOR INSULATOR: PBT, UL94V-0, BLACK
CABLE JACKET: FEP
CABLE DIELECTRIC: FEP
CABLE CENTER CONDUCTOR: COPPER WIRE STRANDED, SILVER PLATED
CABLE OUTER CONDUCTOR: COPPER WIRE BRAID, TIN PLATING





Diagram illustrating the cable marking code: **A-IPAX113-XXXXYZ**

- A**: CONNECTOR ORIENTATION
 - = 0° F=180°
 - C = 90° H=270°
 - G = LEGACY, DO NOT USE FOR NEW DESIGNS
- IPAX**: CABLE TYPE (113 = 1.13MM CABLE)
- 113**: CABLE LENGTH IN MM (L<1000MM)
- XXX**: CABLE COLOR
 - A=ORANGE
 - B=BLACK
 - C=CURRY
 - E=GREEN
 - G=GRAY
 - N=BROWN
- Y**: NUMBER OF TERMINATED ENDS (1 OR 2)
- Z**: CABLE COLOR
 - P=PURPLISH RED
 - R=RED
 - U=BLUE
 - W=WHITE
 - Y=YELLOW

EXAMPLE : 020 = 20MM
150 = 150MM
CHANGE "-" TO "X" (L>=1000MM)
EXAMPLE : 1020 = 1020MM

Amphenol RF	
www.amphenolrf.com	
DRAWING NO.	A-IPAX113-XXXXZ
ITEM NO.	A-IPAX113-XXXXZ
PART NO.	A-IPAX113-XXXXZ