

1534112-1 ✓ ACTIVE

MQS

TE Internal #: 1534112-1

2 Position, Black, Retainer, PBT GF10, -40 – 120 °C [-40 – 248 °F]

[View on TE.com >](#)



Automotive Parts > Automotive Connector Accessories > Automotive Connector Locks & Position Assurance



Number of Positions: 2

Primary Product Color: **Black**

Connector & Contact Retention Accessory Type: **Retainer**

Primary Product Material: **PBT GF10**

Operating Temperature Range: **-40 – 120 °C [-40 – 248 °F]**

Features

Product Type Features

| | |
|--|----------|
| Sealable | No |
| Connector & Contact Retention Accessory Type | Retainer |

Configuration Features

| | |
|---------------------|---|
| Number of Positions | 2 |
|---------------------|---|

Body Features

| | |
|--------------------------|----------|
| Primary Product Color | Black |
| Primary Product Material | PBT GF10 |

Usage Conditions

| | |
|-----------------------------|----------------------------|
| Operating Temperature Range | -40 – 120 °C[-40 – 248 °F] |
|-----------------------------|----------------------------|

Industry Standards

| | |
|------------------------|---------|
| UL Flammability Rating | UL 94HB |
|------------------------|---------|

Packaging Features

| | |
|--------------------|------|
| Packaging Method | Box |
| Packaging Quantity | 6000 |

Other

| | |
|-------------|-----|
| Serviceable | Yes |
|-------------|-----|

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | 有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC |
| Halogen Content | Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Not applicable for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-N02-MUC063
MQS 0.63mm Unsealed Connector System




TE Part # 2315855-6
MSD,REC HSG ASSY,630A,V0,M8



TE Part # 1-1587987-4
FUSE,RECEPTACLE ASSEMBLY, 630A, MSD



TE Part # 1-1587987-3
RECEPTACLE ASSEMBLY, 250A, MSD




TE Part # 1299428-1
CABLE ASSY-LV HVIL EXTN(ASM-001748)



TE Part # 2315855-4
MSD,REC HSG ASSY,450A,V0,M8

Customers Also Bought



Documents

Product Drawings

[MQS RETAINER FOR 2POS REC.HSG](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_1534112-1_B.2d_dxf.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1534112-1_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1534112-1_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

1534112-1

2 Position, Black, Retainer, PBT GF10, -40 – 120 °C [-40 – 248 °F]



Product Specifications

Product Specification

English