







1			2			3			4			5																																																															
																																																																											
									Specifications: Current Rating: 3.0A AC/DC Voltage Rating: 250V AC/DC Contact Resistance: 20m Ohm Max Insulation Resistance: 1000M Ohm Min. Withstanding Voltage: 1000V AC/Minute Operating Temperature Range: -40°C To +105°C																																																																		
									Material and Finish: Insulator: Thermoplastic (UL94V-0) Insulator Color: Beige Contact: Copper Alloy Plating: Gold/Bright Tin Plated																																																																		
How To Order 2600-XX-SXX Blank: Bright Tin Plated G:Gold Plated Blank: Beige W: White No. of Contacts																																																																											
Dimension: <table><tr><th rowspan="2">Circuits</th><th colspan="2">Dimension:</th><th rowspan="2">Circuits</th><th colspan="2">Dimension:</th></tr><tr><th>A</th><th>B</th><th>A</th><th>B</th></tr><tr><td>02</td><td>2.54</td><td>5.08</td><td>12</td><td>27.94</td><td>30.48</td></tr><tr><td>03</td><td>5.08</td><td>7.62</td><td>13</td><td>30.48</td><td>33.02</td></tr><tr><td>04</td><td>7.62</td><td>10.16</td><td>14</td><td>33.02</td><td>35.56</td></tr><tr><td>05</td><td>10.16</td><td>12.70</td><td>15</td><td>35.56</td><td>38.10</td></tr><tr><td>06</td><td>12.70</td><td>15.24</td><td>16</td><td>38.10</td><td>40.64</td></tr><tr><td>07</td><td>15.24</td><td>17.78</td><td>17</td><td>40.64</td><td>43.18</td></tr><tr><td>08</td><td>17.78</td><td>20.32</td><td>18</td><td>43.18</td><td>45.72</td></tr><tr><td>09</td><td>20.32</td><td>22.86</td><td>19</td><td>45.72</td><td>48.26</td></tr><tr><td>10</td><td>22.86</td><td>25.40</td><td>20</td><td>48.26</td><td>50.80</td></tr><tr><td>11</td><td>25.40</td><td>27.94</td><td></td><td></td><td></td></tr></table>												Circuits	Dimension:		Circuits	Dimension:		A	B	A	B	02	2.54	5.08	12	27.94	30.48	03	5.08	7.62	13	30.48	33.02	04	7.62	10.16	14	33.02	35.56	05	10.16	12.70	15	35.56	38.10	06	12.70	15.24	16	38.10	40.64	07	15.24	17.78	17	40.64	43.18	08	17.78	20.32	18	43.18	45.72	09	20.32	22.86	19	45.72	48.26	10	22.86	25.40	20	48.26	50.80
Circuits	Dimension:		Circuits	Dimension:																																																																							
	A	B		A	B																																																																						
02	2.54	5.08	12	27.94	30.48																																																																						
03	5.08	7.62	13	30.48	33.02																																																																						
04	7.62	10.16	14	33.02	35.56																																																																						
05	10.16	12.70	15	35.56	38.10																																																																						
06	12.70	15.24	16	38.10	40.64																																																																						
07	15.24	17.78	17	40.64	43.18																																																																						
08	17.78	20.32	18	43.18	45.72																																																																						
09	20.32	22.86	19	45.72	48.26																																																																						
10	22.86	25.40	20	48.26	50.80																																																																						
11	25.40	27.94																																																																									
P.C.B. Layout						RoHS Compliant																																																																					
F				DRAWN:		GENERAL TOLERANCE:																																																																					
E				Jamie Chuang		.X=±0.20 .XX=±0.15																																																																					
D				CHECKED:		UNIT: MM		ON-SHORE TECHNOLOGY, INC.																																																																			
C				Jerry Chen		SCALE: 1:1																																																																					
B				APPROVAL:		SHEET: 1/2		DESCRIPTION: 2.54mm Wire To Board Wafer Straight Type																																																																			
A	08-Sep-2023		Jamie	Rory Chen		PART NO: 2600-XX-S																																																																					
REV	DATE	FILE	BY			PROJECTION: 